




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2016-02-16	Wes	Change Rev.01 To Rev.A



Conn.

DC-02AMFM-QL8W00
Color: Black



- Note:
- * $\varnothing$ Important Dimension To Check.
 - * Working Voltage Rating: AC 300V
 - * Working Current Rating: Max. 20A
 - * Waterproof Rate: IP68(Mated)
In 1 meters water within 24hours.
 - * Housing: Nylon+GF, Black (UV Resistance)
 - * Female Pin: Copper Alloy, Gold & Ni Plated
 - * Cable: SJTW 12AWG*2C, PVC Jacket,
OD=10.7, Black.
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



Pin Assignments
Front View

DC-02AMFM-QL8DXX
XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
99 : 99Meters
Cable Length(L): 01~99Meters

2	White	白
1	Black	黑
Conn.	Wire Color	
Pin Out		

UNIT:mm		TOLERANCE		TITLE		ITEM NO		DRAWN BY		DATE	
± 0.5				X-Lok D Size Cable Molding 2Pin M Connector F Pin(20A)		DC-02AMFM-QL8EXX		Wes		2016-02-16	
				SCALE 1:1		DWG NO		CHECKED BY		DATE	
				SIZE A4		CUSTOMER		Spring		2016-02-16	
				REV. A		ALTW		APPROVED BY		DATE	
				WC-REV. A.4				Kevin		2016-02-16	
				$\varnothing$ Inspection item							

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[DC-02AMFM-QL8E01](#)