




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2016-02-16	Wes	Change Rev.01 To Rev.A



Pin Assignments
Front View

5	Brown	棕
4	Red	紅
3	Green	綠
2	White	白
1	Black	黑
Conn.	Wire Color	
Pin Out		

DC-05AFFM-QL8EXX

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
99 : 99Meters

Cable Length(L): 01~99Meters

- Note:
- * Ⓢ Important Dimension To Check.
 - * Working Voltage Rating: AC 300V
 - * Working Current Rating: Max. 20A
 - * Waterproof Rate: IP68(Mated)
In 1 meters water within 24hours.
 - * Housing: Nylon+GF, Black(UV Resistance)
 - * Female Pin: Copper Alloy, Gold & Ni Plated
 - * Cable: SJTW 12AWG*5C, PVC Jacket,
OD=13.6, Black.
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TOLERANCE ±0.5		TITLE X-Lok D Size Cable Molding 5Pin F Connector F Pin(20A)		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY Wes		DATE 2016-02-16	
SCALE 1:1		SIZE A4		SHEET 1 OF 1		DWG NO DC-05AFFM-QL8EXX		CHECKED BY Spring		DATE 2016-02-16		APPROVED BY Kevin	
REV. A		WC-REV. A.6		QC: Inspection item		CUSTOMER ALTW		DATE 2016-02-16		DATE 2016-02-16		DATE 2016-02-16	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[DC-05AFFM-QL8E01](#)