



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE31140022~227	2011/04/11	Vicky	Modify Note.
C	LEN1530093~099	2015/02/10	Ruru	Change Logo
D	LEN1681365~371	2016/08/05	Joyy	Modify The SR



Shell	Drain	地線		
13	Black/White	黑/白	26	Gray/Black 灰/黑
12	Light Green	淺綠	25	Green/Black 綠/黑
11	Purple	紫	24	Yellow/Black 黃/黑
10	Orange	橘	23	Pink/Red 粉紅/紅
9	Black	黑	22	Pink/Back 粉紅/黑
8	Red	紅	21	Orange/Black 橘/黑
7	Pink	粉紅	20	Red/Black 紅/黑
6	Gray	灰	19	Puple/White 紫/白
5	Yellow	黃	18	Blue/White 藍/白
4	Green	綠	17	Green/White 綠/白
3	White	白	16	Orange/White 橘/白
2	Blue	藍	15	Red/White 紅/白
1	Brown	棕	14	Brown/White 棕/白
Conn.	Wire Color		Conn.	Wire Color



- Note:**
- * **Important Dimension.**
 - * Waterproof Rate: IP67
 - * Housing: ABS, Black
 - * Female Pin: Copper Alloy, Gold Plated.
 - * Gasket: EPDM, Black
 - * Screw: Steel, Nickel Plated.
 - * Cable: UL2464 26AWG*26C+Drain+Al/My, PVC Jacket (UV Resistant), OD=8.0mm, Black.
 - * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30~: ±200mm
31M~99M: ±500mm

UNIT:mm		TITILE		ITEM NO		DRAWN BY		DATE	
TOLERANCE		High Density D-SUB		HDB-26AFFM-SL7AXX		Joyy		2016-08-05	
.X ±0.25		Cable Screw 26P F Conn F Pin		DWC NO		CHECKED BY		DATE	
.XX ±0.1		SCALE 1:2		ALTW		Ma Fei		2016-08-05	
.XXX ±0.05		SIZE A4		CUSTOMER		APPROVED BY		DATE	
ANGLES ±1°		REV. D		ALTW		Jerry		2016-08-05	
		WC-REV. A.2							
		SHEET 1 OF 1							
		QC: Inspection item							

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[HDB-26AFFM-SL7A02](#) [HDB-26AFFM-SL7A10](#) [HDB-26AFFM-SL7A01](#) [HDB-26AFFM-SL7A05](#)