









REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8B0245	2008/10/03	Shin	Add Note



Pin Assignments
Front View



Recommended
Panel Cut-Out



Note:

- * $\varnothing$ Important Dimension.
- * Waterproof Rate: IP67
- * Housing: Black, Nylon+GF
- * Pin: Copper Alloy, Gold Plated.
- * Nut: Black, Nylon+GF
- * Gasket: Black, EPDM

- $\triangle B$ * Use with waterproof cap or dust cap
Maximum Panel Thickness: 3.0mm
- $\triangle B$ * Use without waterproof cap or dust cap
Maximum Panel Thickness: 4.0mm

UNIT:mm	
TOLERANCE	
.X	±0.25
.XX	±0.1
.XXX	±0.05
ANGLES	±1°

TITLE Middle, Panel Screw 3Pin M Conn M Pin			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	
REV. B	WC-REV. A.2	$\varnothing$ Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO. CC-03RMMS-SC7001	DRAWN BY SamChang	DATE 2012-04-10
DWG NO. CC-03RMMS-SC7001	CHECKED BY Jeffrey	DATE 2012-05-10
CUSTOMER ALTW	APPROVED BY Lion	DATE 2012-05-10

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CC-03RMMS-SC7001](#)