







THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF AMPHENOL LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY AMPHENOL LTW.



- Note:
- * @@Important Dimensions To Check.
 - * Waterproof Rate: IP67
 - * Female Housing: Nylon+GF, Black
 - * Female Pin: Copper Alloy, Tin Plated
 - * Pin Screws: 1.5mm(HEX), Stainless Steel
For wire assembly, tightened by tool.
 - * O-ring: Silicone, Gray
 - * Seal 1:For Cable OD: $\phi 6.0\text{mm} \sim 9.0\text{mm}$
 - * Seal 2:For Cable OD: $\phi 9.0\text{mm} \sim 12.5\text{mm}$
 - * Flame Class: UL94V-0
 - ⑧ * One Set Unassembled in one PE Bag
 - * 1.5mm Hex Tool for Screws sold separately
 - △ * Wire Size Range: 14AWG~18AWG



Pin Assignments
Front View



Conn.

UNIT:mm		TOLERANCE		TITLE		Amphenol LTW		ITEM NO	DRAWN BY	DATE
±0.5 mm		Assy Female Power Conn. 16Amp Screw in Type Pin (Tin Plated)		安費諾亮泰企業股份有限公司		PWG-04BFFB-SL7003		PWG-04BFFB-SL7003	baowei	2011/08/27
SCALE		Free		SHEET		PWG-04BFFB-SL7003		DWG NO	CHECKED BY	DATE
REV. B		SIZE A4		1 OF 1		ALTW		PWG-04BFFB-SL7003	Micky	2011/08/27
				QC :Inspection Item				CUSTOMER	APPROVED BY	DATE
									Victor	2011/08/27

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[PWG-04BFFB-SL7003](#)