




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1480450~453	2014/08/14	Sam	Change Logo



Conn.




PWC-03AFMM-LL7100
Color:Black

PWC-03AFMM-LL7DXX

XX :01~99Meters
01 :01Meter
02 :02Meters
:
:
99 :99Meters

Cable Length(L):01~99Meters

Note:
* QC Important Dimension To Check.
* Waterproof Rate: IP67
* Connector: Nylon+GF, Black.
* Male Pin: Copper Alloy, Gold Plated.
* Lock Nut: Nylon+GF, Black.
* Cable: UL SJTW 14AWG*3C·PVC Jacket
UV Resistant, OD=9.5, Black.
* Cable Length Tolerance: 01M:40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



Pin Assignments
Front View

3	White	白
2	Green	綠
1	Black	黑
Conn.	Wire Color	
Pin Out		

UNIT:mm		TITLE	POWER MOLDING F CONN. M PIN 20A		
TOLERANCE		SCALE	SIZE	SHEET	OF
±0.5 mm		1:1	A4	1	1
REV.	B	WC-REV.	A.2	<u>QC</u> : Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE
ALTW	Sam	2014-08-14
	Vicky	2014-08-14
	Rita	2014-08-14

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[PWC-03AFMM-LL7D05](#) [PWC-03AFMM-LL7D02](#) [PWC-03AFMM-LL7D01](#) [PWC-03AFMM-LL7D10](#)