

1		2		3		4		5		6		7		8	
								REV.		ECN NO.		DATE		SIGN	

Note:

- * @Important Dimension.
- * Waterproof Rate : IP68
IP68:1M of depth of water 24 hours
(防水等級 IP68)
(IP68:1米水深 24小時)
- * Do Mating Test After Glued
點膠後,須作對插測試
- * HD-SUB Conn. :Black Core , PBT
- * Plastic Jacket : Black , Nylon+GF
- * Pin : Copper Alloy , Gold Plated
- * Ring : Light Blue,Silicone
- * Screw : Copper Alloy,Nickel Plated,#4-40 UNC

Panel Thickness
面板厚度
(Max.)
X

Screw L=5.0 For Panel Thickness Under 1.2mm
適用板厚為 1.2mm 以下

Screw L=6.0 For Panel Thickness Between 1.2~2.0mm
適用板厚為 1.2~2.0mm

Recommended Panel Cut-Out
建議挖孔尺寸

UNIT:mm		TITLE D-SUB Conn. Panel Screw HD15P M Conn. M Pin		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO HDB-15PMMP-SR8001		DRAWN BY DongYaLi		DATE 2006/12/16	
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE Free		SHEET 1 OF 1		DWG NO HDB-15PMMP-SR8001		CHECKED BY Simon		DATE 2006/12/16	
		REV. A		SIZE A4		CUSTOMER ALTW		APPROVED BY Max		DATE 2006/12/16	

1		2		3		4		5		6		7		8	

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[HDB-15PMMP-SR8001](#)