



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE313A0308	2013-10-15	Raison	Modify Gasket Note.and H Cut
C	LEN1440095~97	2014-04-04	Tom_gu	Change H Cut To D Cut



Cable Length(L):100~1000mm

RCP-5SPFFP-SCM7BXX


XX: 100~1000mm
10: 100mm
15: 150mm
20: 200mm
95: 950mm
A0: 1000mm



Cable length	Tolerance
0.0~100 mm	±10 mm
101~300 mm	±15 mm
301~1000 mm	±20 mm

Note:

- * $\varnothing$ Important Dimension
- * Waterproof Rate : IP67 Mated
- * Housing : Nylon+GF,UL 94V-0,BLACK
- * Screw Nut : Nylon+GF,BLACK
- * Gasket : Silicone,UL 94V-0,Gray.
- * PCB: FR-4
- * Jack : PBT Polyester UL 94V-0
- * Use without Waterproof cap or Dust cap
For Panel Thickness Max: 4.2mm
- * Use with Waterproof cap or Dust cap
For Panel Thickness Max: 3.0mm
- * Screw torsion value range: 8~12kgf-cm



Shield	Drain Wire	接地線	Shield
8	Brown	棕	8
7	White/Brown	白/棕	7
6	Green	綠	6
5	White/Blue	白/藍	5
4	Blue	藍	4
3	White/Green	白/綠	3
2	Orange	橘	2
1	White/Orange	白/橘	1
Jack	Wire Color	Plug	
Pin Out			

Recommended Panel Cut-out Rear View

Dimensions: 19.4 ± 0.1, 20.8 ± 0.1

UNIT:mm			TITLE RJ45,C SIZE,MATED WATERPROOF
TOLERANCE	±0.25	SCALE 1:1	SIZE A4
.X	±0.1	SHEET 1	OF 1
.XX	±0.05	REV. C	WC-REV. B.4
.XXX	±1°	$\varnothing$ Inspection item	
ANGLES			

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Tom_gu	DATE 2014-04-04
DWG NO RCP-5SPFFP-SCM7BXX	CHECKED BY Tony	DATE 2014-04-04
CUSTOMER ALTW	APPROVED BY Victor	DATE 2014-04-04

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RCP-5SPFFP-SCM7B20](#) [RCP-5SPFFP-SCM7B15](#)