



1	2	3	4	5	6	7	8
REV.				ECN NO.	DATE	SIGN	DESCRIPTION



Plug

RCP-5UAMMM-TRM7AXX

XX: 01~99Meter
01: 01Meter
02: 02Meters

:



99: 99Meters

Cable Length(L):01~99Meters

X:
(A)CAT5E UTP

Note:

- * Important Dimension
 - * Waterproof Rate: IP67.
 - * Plug: PC, UL94V-2, Gold Plated,
 - * Lock Nut: Nylon+GF, Black.
 - * Gasket: EPDM, Black.
 - * Cable: (A)CAT5E UTP, OD Max.: $\varnothing 6.0$, Black.
 - * Cable Length Tolerance:
- | | |
|---------|--------------|
| 01M: | ± 40 mm |
| 02~05M: | ± 60 mm |
| 06~10M: | ± 100 mm |
| 11~30M: | ± 200 mm |
| 30~99M: | ± 500 mm |




Pin Out

Wire Color		Plug
Drain Wire	接地	
Brown	棕	8
Brown/white	棕白	7
Green	綠	6
Blue/white	藍白	5
Blue	藍	4
Green/white	綠白	3
Orange	橙	2
Orange/white	橙白	1

Twist
對絞Twist
對絞Twist
對絞Twist
對絞

UNIT:mm



TITLE
RJ45,C SIZE,RIGHT ANGLE
CABLE 3P_LOCK 5E M CONN M PIN

TOLERANCE
.X ± 0.25
.XX ± 0.1
.XXX ± 0.05
ANGLES $\pm 1^\circ$

SCALE
1:1SIZE
A4SHEET
1 OF 1REV.
AWC-REV.
A.10

Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Laurence_zang	DATE 2013-04-20
DWG NO RCP-5UAMMM-TRM7AXX	CHECKED BY RAISON	DATE 2013-04-20
CUSTOMER ALTW	APPROVED BY VICTOR	DATE 2013-04-20

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RCP-5UAMMM-TRM7A01](#)