



Conn

PWC-03AMFM-LL7000

PWC-03AMFM-LL7BXX

```
XX:01~99Meters
01:01Meter
02:02Meters
:
:
99:99Meters
```


- *  Important Dimension To Check.
- * Waterproof Rate: IP67(Mated)
- * Connector: Nylon+GF, Black
- * Female Pin: Copper Alloy, Gold Flash
- * Cable: TC-ER, 14AWG*3C
PVC Jacket, OD=9.7mm, Black
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



Pin Assignments Front View

3	White	白
2	Green	緑
1	Black	黒
Housing	Wire Color	
Pin Out		

UNIT: mm



TOLERANCE	
.X	± 0.25
.XX	± 0.1
.XXX	± 0.05
ANGLES	$\pm 1^{\circ}$

TITLE	Power Molding M Conn. F Pin 20Amps
-------	---------------------------------------

SCALE 1 : 1	SIZE A4	SHEET 1 OF 1
REV. B	WC-REV. .0	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO PWC-03AMFM-LL7BXX	CHECKED BY Jimmy	DATE 2012-12-13
CUSTOMER ALTW	APPROVED BY Victor	DATE 2012-12-13

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[PWC-03AMFM-LL7B01](#) [PWC-03AMFM-LL7B02](#)