



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1480459~462	2014/08/15	Sam	Change Logo




Conn.




Cable 2

PWC-03AMFM-LL7100
Color:Black



Pin Assignments
Front View



PWC-03AMFM-LL7DXX

XX :01~99Meters
01 :01Meter
02 :02Meters

99 :99Meters

Cable Length(L):01~99Meters

- Note:
- * $\varnothing$ Important Dimension To Check.
 - * Waterproof Rate: IP67
 - * Connector: Nylon+GF, Black.
 - * Female Pin: Copper Alloy, Gold Plated.
 - * Cable: UL SJTW 14AWG*3C·PVC Jacket
UV Resistant, OD=9.5, Black.
 - * Cable Length Tolerance: 01M:40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

3	White	白
2	Green	綠
1	Black	黑
Conn.	Wire Color	
Pin Out		

UNIT:mm		TOLERANCE ±0.5 mm		TITLE POWER MOLDING M CONN. F PIN 20A		SCALE 1:1		SIZE A4		SHEET 1 OF 1		REV. B		WC-REV. A.2		QC:Inspection item		ITEM NO PWC-03AMFM-LL7DXX		DRAWN BY Sam		DATE 2014-08-15	
																		CUSTOMER ALTW		CHECKED BY Vicky		DATE 2014-08-15	
																				APPROVED BY Rita		DATE 2014-08-15	

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[PWC-03AMFM-LL7D10](#) [PWC-03AMFM-LL7D02](#) [PWC-03AMFM-LL7D05](#) [PWC-03AMFM-LL7D01](#)