




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2007/11/23	Robert Hsu	
B	LEN-040111~14	2010/04/12	Tao-Cheng	Change Cable OD
C	LEN15A0226~29	2015/10/13	Jason.Yu	Update LOGO & Title



HDB-62AMMM-SL7AXX

XX : 01~99Meters
01 : 01Meters
02 : 02Meters
...

99 : 99Meters

Cable Length(L):01~99Meters

Note:

- * (QC) Important Dimension To Check.
- * Waterproof Rate: IP67
- * Housing: ABS, Black
- * Conn.: D-Sub 62 Pin, Male
- * Gasket: EPDM, Black
- * Screw: Big EPC
- * Cable: UL2464 (3IC*26#+MY)+3IC*26#+AL/MY+D, PVC Jacket(UV Resistant), OD=13.0, Black
- * Cable Length Tolerance: 1M~10M±5%mm, 11M~99M±500mm.




UNIT:mm
TOLERANCE
±0.5 mm

TITLE △ HD SUB 62P M CONN CABLE SCREW HD62P M CONN M PIN			
SCALE 7:10	SIZE A4	SHEET 1 OF 2	
REV. C	WC-REV. A.1	(QC): Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Jason.Yu	DATE 2015/10/13
DWG NO HDB-62AMMM-SL7AXX	CHECKED BY Doreen	DATE 2015/10/13
CUSTOMER ALTW	APPROVED BY Lisa	DATE 2015/10/13

1			2		3			
F					Shell	Drain	地線	
	31	Light Blue/Red 亮藍/紅		62	Light Blue/Red 亮藍/紅			
	30	Light Blue/Black 亮藍/黑		61	Light Blue/Black 亮藍/黑			
	29	Light Blue 亮藍		60	Light Blue 亮藍			
	28	Pink/Green 粉紅/綠		59	Pink/Green 粉紅/綠			
E	27	Pink/Blue 粉紅/藍		58	Pink/Blue 粉紅/藍			
	26	Pink/Red 粉紅/紅		57	Pink/Red 粉紅/紅			
	25	Pink/Black 粉紅/黑		56	Pink/Black 粉紅/黑			
	24	Gray/Black 灰/黑		55	Gray/Black 灰/黑			
	23	Green/Black 綠/黑		54	Green/Black 綠/黑			
D	22	Yellow/Black 黃/黑		53	Yellow/Black 黃/黑			
	21	Orange/Black 橘/黑		52	Orange/Black 橘/黑			
	20	Red/Black 紅/黑		51	Red/Black 紅/黑			
	19	Purple/White 紫/白		50	Purple/White 紫/白			
	18	Blue/White 藍/白		49	Blue/White 藍/白			
C	17	Green/White 綠/白		48	Green/White 綠/白			
	16	Orange/White 橘/白		47	Orange/White 橘/白			
	15	Red/White 紅/白		46	Red/White 紅/白			
	14	Brown/White 棕/白		45	Brown/White 棕/白			
	13	Black/White 黑/白		44	Black/White 黑/白			
B	12	Light Green 亮綠		43	Light Green 亮綠			
	11	Pink 粉紅		42	Pink 粉紅			
	10	White 白		41	White 白			
	9	Gray 灰		40	Gray 灰			
	8	Purple 紫		39	Purple 紫			
A	7	Blue 藍		38	Blue 藍			
	6	Green 綠		37	Green 綠			
	5	Yellow 黃		36	Yellow 黃			
	4	Orange 橘		35	Orange 橘			
	3	Red 紅		34	Red 紅			
	2	Brown 棕		33	Brown 棕			
	1	Black 黑		32	Black 黑			
	Conn.	Wire Color		Conn.	Wire Color			
	Group1 Pin Out				Group1 Pin Out			
	UNIT:mm				TITLE		HD SUB 62P M CONN	
TOLERANCE				CABLE SCREW HD62P M CONN M PIN				
±0.5 mm		SCALE 7:10		SIZE A4		SHEET 2 OF 2		
		REV. C		WC-REV. A.1		QC: Inspection item		



Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	Jason.Yu	2015/10/13
CUSTOMER	Doreen	2015/10/13
ALTW	Lisa	2015/10/13

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[HDB-62AMMM-SL7A02](#) [HDB-62AMMM-SL7A01](#) [HDB-62AMMM-SL7A05](#)