








1	2	3	4	5	6	7	8																								
				REV.	ECN NO.	DATE	SIGN	DESCRIPTION																							
																															
								Panel Thickness 面板厚度 X(Max.) Screw L=5.0 For Panel Thickness Under 1.2mm 適用板厚為1.2mm以下 Screw L=6.0 For Panel Thickness Between 1.2~2.0mm 適用板厚為1.2~2.0mm																							
				Note: * @@Important Dimension. * Waterproof Rate : IP68 IP68:1M of depth of water 24 hours (防水等級 IP68) (IP68:1米水深 24小時) * Do Mating Test After Glued 點膠後,須作對插測試 * HD-SUB Conn. :Black Core , PBT * Plastic Jacket : Black , Nylon+GF * Pin : Copper Alloy , Gold Plated * Ring : Light Blue,Silicone * Screw : Copper Alloy,Nickel Plated,#4-40 UNC																											
UNIT:mm TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°				TITLE D-SUB Conn. Panel Screw HD26P M Conn. M Pin SCALE Free SHEET 1 OF 1 REV. A SIZE A4 @@ :Inspection Item				Amphenol LTW 安費諾亮泰企業股份有限公司				ITEM NO HDB-26PMMP-SR8001 DWG NO HDB-26PMMP-SR8001 CUSTOMER ALTW				DRAWN BY Gao Ling CHECKED BY Simon APPROVED BY Max				DATE 2006/12/09 DATE 2006/12/09 DATE 2006/12/09											
1				2				3				4				5				6				7				8			

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[HDB-26PMMP-SR8001](#)