




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-990077	2009/08/18	Vicky	Remove Pin Dim.
C	LEN1390205	2013/09/02	Lu Di	Update Dimension



✓ With Liquid Glue
點防水膠




Note:

- *  Important Dimension.
- * Waterproof Rate: IP68
IP68: 1M of depth of water 24 hours
(防水等級: IP68)
(IP68: 1米水深24小時)
- * Do Mating Test After Glued
點膠後，須作對插測試
- * Housing: Black, Nylon+GF.
- * Connector: Black, PBT.
- * Male Pin: Copper Alloy, Gold Plated.
- * Ring: Silicone, Light Blue.
- * Screw: Copper Alloy, Nickel Plated, #4-40 UNC.
- * Applicable Wire Range: 24AWG-28AWG.
適用電線範圍: 24AWG-28AWG

Panel Thickness
面板厚度

Screw L=5.0 For Panel Thickness
Under 1.2mm
適用板厚為 1.2mm 以下

Screw L=6.0 For Panel Thickness
Between 1.2~2.0mm
適用板厚爲1.2~2.0mm



Recommended Panel Cut-Out
建議挖孔尺寸

UNIT:mm			TITLE D-SUB Conn. Panel Screw HD26P M Conn. M Pin			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO HDB-26PMMS-SL800I		DRAWN BY Di_lu		DATE 2013/09/02			
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°			SCALE 1:1		SIZE A4			DWG NO HDB-26PMMS-SL800I		CHECKED BY Mafei		DATE 2013/09/02			
			REV. C		WC-REV. A.3			CUSTOMER ALTW		APPROVED BY Victor		DATE 2013/09/02			
			QC: Inspection item												
		2		3		4		5		6		7		8 FMM10702-01-02A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[HDB-26PMMS-SL8001](#)