





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1720207	2017-02-13	Frank Deng	Change dimension from 34.0 to 34.7



Pin Assignments
Front View

3	Red	紅
2	Brown	棕
1	Black	黑
Conn.	Wire Color	
Pin Out		

BB-03AFMM-QR8DXX

XX :01~99Meters
01 :01Meter
02 :02Meters
:
99 :99Meters

- Note:
- * Ⓞ Important Dimension To Check.
 - * Waterproof Rate: IP68(Mated)
 - * Working Voltage Rating: AC 300 V
 - * Working Current Rating: 10A
 - * Flame Class: UL94V-0 (UV Resistance)
 - * Housing: Nylon+GF, Black.
 - * Male Pin: Copper Alloy, Gold Plated.
 - * Rubber: Silicon, Gray
 - * Cable: UL21388 16AWG*3C+AL+My
PVC Jacket UV Resistant, OD=6.5, Black.
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TOLERANCE .X ±0.5		TITLE X-Lok B-Size Molding F Conn M 3 Pin		ITEM NO		DRAWN BY Frank Deng		DATE 2017-02-13	
SCALE 6:5		SIZE A4		SHEET 1 OF 1		DWG NO BB-03AFMM-QR8DXX		CHECKED BY Spring Liu		DATE 2017-02-13	
REV. B		WC-REV. A.2		QC: Inspection item		CUSTOMER ALTW		APPROVED BY Kevin Hu		DATE 2017-02-13	

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BB-03AFMM-QR8D01](#)