









REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8B0254	2008/10/03	Shin	Add Note



Pin Assignments
Front View



Recommenderd Panel Cut-Out



Note:

- * $\varnothing$ Important Dimension To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black.
- * Pin: Copper Alloy, Gold Plated.
- * Nut: Nylon+GF, Black.
- * Gasket: EPDM.Black.

$\triangle B$ * Use with waterproof cap or dust cap
Maximum Panel Thickness: 3.0mm

$\triangle B$ * Use without waterproof cap or dust cap
Maximum Panel Thickness: 4.0mm

UNIT:mm		TITLE
TOLERANCE		Middle, Panel Screw 7Pin M Conn. F Pin
.X ±0.25		SCALE 1:1
.XX ±0.1		SIZE A4
.XXX ±0.05		SHEET 1 OF 1
ANGLES ±1°		REV. B
		WC-REV. A.2
		$\varnothing$ Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	CD-07RMFS-SC7001	DRAWN BY	SamChang	DATE	2012-04-11
DWG NO	CD-07RMFS-SC7001	CHECKED BY	Jeffrey	DATE	2012-05-15
CUSTOMER	ALTW	APPROVED BY	Lion	DATE	2012-05-15

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CD-07RMFS-SC7001](#)