



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



REV.	ECN NO.	DATE	SIGN	DESCRIPTION



CC-02AMFM-QL8W00 ①
Color: Black

CC-02AMFM-QL8EXX
XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
:
99 : 99Meters

- Note:
- * ① Important Dimension To Check.
 - * Working Voltage Rating: AC 300V
 - * Working Current Rating: 20A
 - * Flame Class: UL94V-0 (UV Resistance)
 - * Waterproof Rate: IP68(Mated)
 - * Housing: Nylon+GF, Black
 - * Female Pin: Copper Alloy, Gold Plated
 - * Cable: SJTW 12AWG*2C, Black
PVC Jacket, OD=10.7mm.
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



Pin Assignments
Front View

2	White	白
1	Black	黑
Conn.	Wire Color	
	Pin Out	

UNIT:mm		TOLERANCE ±0.5		TITLE X Lok C-Size Cable 2 Pin 20A M Conn. F Pin		ITEM NO		DRAWN BY Micky		DATE 2014-12-04	
SCALE 1:1		SIZE A4		SHEET 1 OF 1		DWG NO CC-02AMFM-QL8EXX		CHECKED BY Spring		DATE 2014-12-04	
REV. A		WC-REV. A.1		QC: Inspection item		CUSTOMER ALTW		APPROVED BY Kevin		DATE 2014-12-04	

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CC-02AMFM-QL8E01](#)