




1	2	3	4	5	6	7	8	
				REV. B	ECN NO. LEN1620170~173	DATE 2016/01/14	SIGN Ruru	DESCRIPTION Change Logo & Note



Conn.



① CBD-08BFFM-LL6000
Color: Black



② Cable

CBD-08BFFM-LL6AXX


XX:01~99Meter
01:01Meter
02:02Meters
⋮
99:99Meters


Cable Length(L):01~99Meters

8	Green	20
7	Blue	20
6	Yellow	24
5	Orange	24
4	Red	24
3	Brown	24
2	Black	24
1	Purple	24
Conn.	Wire Color	AWG

Pin Out

Pin Assignments
Front View





Note:

- * @C Important Dimensions To Check.
- * Waterproof Rate: IP66
- * Housing: Nylon+GF, Black
- * Female Pin: Copper Alloy, Gold Plated
- * O-Ring: EPDM, Black
- * Nut: Nylon+GF, Black
- * Cable: UL2464 (20AWG*2C+24AWG*6C)+Drain+Al/My, PVC Jacket UV Resistant(+105°C~-20°C), OD=6.0M Black
- * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

UNIT:mm		TITLE	Middle,Cable Lock 8Pin F Conn F Pin		ITEM NO	DRAWN BY	Ruru	DATE	2016/01/14
TOLERANCE	±0.5 mm	SCALE	Free	SHEET 1 OF 1	DWG NO	CHECKED BY	Rita	DATE	2016/01/14
REV. B	SIZE A4	QC	:Inspection Item		CUSTOMER	APPROVED BY	Lisa	DATE	2016/01/14

Amphenol LTW

安費諾亮泰企業股份有限公司

8 FMW0702-01-01A2

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF AMPHENOL LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY AMPHENOL LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CBD-08BFFM-LL6A05](#) [CBD-08BFFM-LL6A01](#) [CBD-08BFFM-LL6A02](#) [CBD-08BFFM-LL6A10](#)