



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION





Conn.

CD-07AMFM-QL8W00
Color: Black

CD-07AMFM-QL8DXX

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
:
99 : 99Meters

- Note:
- * $\varnothing$ Important Dimension To Check.
 - * Working Voltage Rating: AC 300V
 - * Working Current Rating: 5A
 - * Flame Class: UL94V-0 (UV Resistance)
 - * Waterproof Rate: IP68(Mated)
 - * Housing: Nylon+GF, Black
 - * Female Pin: Copper Alloy, Gold Plated
 - * Cable: UL21388 20AWG*7C+AL/PET Tape
Black ,PVC Jacket UV Resistant, OD=6.8
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



Pin Assignments
Front View

7	Orange	橙
6	Blue	藍
5	Purple	紫
4	Yellow	黃
3	Black	黑
2	Red	紅
1	White	白
Conn.	Wire Color	
Pin Out		

UNIT:mm		TOLERANCE ±0.5		TITLE X Lok C-Size Cable 7 Pin 5A M Conn. F Pin		ITEM NO		DRAWN BY Micky		DATE 2014-12-12	
SCALE 1:1		SIZE A4		SHEET 1 OF 1		DWG NO CD-07AMFM-QL8DXX		CHECKED BY Spring		DATE 2014-12-12	
REV. A		WC-REV. A.1		QC: Inspection item		CUSTOMER ALTW		APPROVED BY Kevin		DATE 2014-12-12	

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CD-07AMFM-QL8D01](#)