




1	2	3	4	5	6	7	8	
				REV. B	ECN NO. LEN1620174~177	DATE 2016/01/14	SIGN Ruru	DESCRIPTION Change Logo & Note



Conn.



① CBD-08BFFM-SL6000
Color: Black




② Cable

CBD-08BFFM-SL6AXX


XX:01~99Meter
01:01Meter
02:02Meters
...
99:99Meters

Cable Length(L):01~99Meters



Pin Assignments
Front View

8	Green	20
7	Blue	20
6	Yellow	24
5	Orange	24
4	Red	24
3	Brown	24
2	Black	24
1	Purple	24
Conn.	Wire Color	AWG
Pin Out		



Note:

- * @C Important Dimensions To Check.
- * Waterproof Rate: IP66
- * Housing: Nylon+GF, Black
- * Female Pin: Copper Alloy, Gold Plated
- * O-Ring: EPDM, Black
- * Nut: Nylon+GF, Black
- * Cable: UL2464 (20AWG*2C+24AWG*6C)+Drain+Al/My, PVC Jacket UV Resistant(+105°C~-20°C), OD=6.0, Black
- * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

UNIT:mm

TOLERANCE ±0.5 mm

TITLE Middle,Cable Screw 8Pin F Conn F Pin

SCALE Free SHEET 1 OF 1

REV. B SIZE A4 @C :Inspection Item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

DWG NO CBD-08BFFM-SL6AXX

CUSTOMER ALTW

DRAWN BY Ruru

CHECKED BY Rita

APPROVED BY Lisa

DATE 2016/01/14

DATE 2016/01/14

DATE 2016/01/14

1

2

3

4

5

6

7

8 FMW0702-01-01A2

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CBD-08BFFM-SL6A05](#) [CBD-08BFFM-SL6A10](#) [CBD-08BFFM-SL6A01](#) [CBD-08BFFM-SL6A02](#)