




LAYOUT FOR P.C.B  
CONNECTOR SIDE VIEW



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE PRODUCT SPECIFICATION GS-12-446

NOTE-1: 2 PEGS AT EACH END ONLY

NOTE-2: CAVITY FOR CODING KEY MOUNTING AND CABLE CONNECTOR LATCH.

NOTE-3: IF SUFFIX "P" IS ADDED IN P/N PACKAGING IS IN TRAYS  
BUT CONNECTOR MARKING IS WITHOUT "P"  
EXAMPLE: HM1W52DTR400H6P, MARKED HM1W52DTR400H6

NOTE-4: P.C.B HOLES DEFINITION - SEE GS-12-446

SPECIFIC DATAS:

Visual inspection : 100%

- Marking failures
- Housing material failures
- Spoilt housing
- Stained housing
- Broken contacts ( twisted or loosen )

TIN LEAD PART NUMBER

PART NUMBER | HM1W52DTR400H6P

LEAD FREE PART NUMBER

PART NUMBER | HM1W52DTR400H6PLF

0.76 um Au & LEAD FREE PART NUMBER

PART NUMBER | HM1W52DTR400HEPLF

European Views

www.fciconnect.com				surface ISO 1302	tolerance std ISO 406 ISO 1101	projection	mm	
				TOLERANCES UNLESS OTHERWISE SPECIFIED				
Dr	Michael Song	2014/12/03	Angular	Linear	0.X	±0.1	size A3	Scale 2.5
Eng	MICHAEL SONG	2014/12/03			0.XX	±0.1		
Chr	ZHEN LUO	2014/12/03			0.XXX	±0.1	ECN ELX-DG-19619	
Appr	COLLINS LU	2014/12/03	Product family	METRAL	Spec ref	-		
FCI				METRAL STRAIGHT HEADER				
SP 400				dwg no C-8626-11115				
catalog no				Rev. E				
CUSTOMER sheet 1 of 1								

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[HM1W52DTR400HEPLF](#)