







PERFORMANCE CHARACTERISTICS

1.5 A AT 20°C (FULLY LOADED)
 CURRENT RATING: 1 A AT 70°C (FULLY LOADED)
 RATED VOLTAGE: 500 V AC (CONT /CONT)
 OPERATING TEMPERATURE : -55°C TO 125°C
 CONTACT RESISTANCE : 20 mΩ MAX
 INSERTION FORCE: 0.75N MAX/CONT
 EXTRACTION FORCE : 0.15N MIN /CONT
 INSULATION RESISTANCE: 10⁴ MΩ MIN

NOTES

- LEAD FREE INDICATOR :LF=LEAD FREE
- THIS PRODUCT IS CSA APPROVED.
THIS PRODUCT IS UL RECOGNIZED.
- FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING :BS.A.201572.001
- THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008

Material		Spec ref		
Mat code		✓	TOLERANCE	
Heat treat			1DEC ±0.2 1DEC	MM
Plating/Finish			2DEC ±0.1 2DEC	
Dr	10-2-92	J.V.B.	size	Scale
Eng			A1	5.000
Chr			Model Name	ECN
Appr			Model Revision	REL Level
A FCI		BSC201418046		Rev. B

rev	ecn no	dr	date
A	104-0018	ALEX B	18-03-04
B	DG05-0493	kasom	11-22-05
-	-	-	-
-	-	-	-
-	-	-	-

PDM: Rev.B

STATUS: Released

Printed: May 25, 2009

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[HM2R02PE5100N9LF](#)