




NOTES: UNLESS OTHERWISE SPECIFIED;

- CONNECTOR MATERIALS:
HOUSING: GLASS FILLED THERMOPLASTIC, UL94-V0 COMPLIANT
KEEPER: GLASS FILLED THERMOPLASTIC, UL94-V0 COMPLIANT
TERMINAL: PHOSPHOR BRONZE ALLOY
- PACKED IN TUBES.
- FEATURE MAY OR MAY NOT BE PRESENT DEPENDING UPON THE MOLD TOOL USED TO PRODUCE PRODUCT.
- PRODUCT SPECIFICATION: GS-12-177.
- APPLICATION SPECIFICATION: GS-20-015.
- THE PRODUCTS WHERE THE PART NUMBER ENDS IN 'LF' MEET THE EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- ALL PRODUCTS WILL WITHSTAND EXPOSURE TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.






TABLE 2

CODE	CONTACT AREA	PERFORMANCE LEVEL
6	0.75um Au min over 1.3um Ni min or 0.68um PdNi min +0.08um Au min over 1.3um Ni min	TELCORDIA CO



mat'l code				tolerances unless otherwise specified		CUSTOMER COPY		FCI			
ltr	ecn no	dr	date	linear	NONE±3	projection		www.fciconnect.com			
E	V04-1123	TAB	02/03/05		.X±0.5			title			
F	V05-0437	VS	07/14/05		.XX±0.13			T SERIES R/A RECEPTACLE			
G	DG06-0378	KL	09/01/06	angles	0°±1°			ASSY, 4 ROW, 6 MOD, STB			
H	DG06-0437	Cenh	10/26/06	dr	V.SEBASTIAN	07/14/05		product family		METRAL	
J	DG08-0173	TER	7/10/08	enr	J.VOLSTROF	07/14/05		size		dwg no	
				chr	J.VOLSTROF	07/14/05		A		SE96892	
				app	J.VOLSTROF	07/14/05		scale		4:1	
sheet	revision	J									
index	sheet	1									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[HM1F49TBP961H6LF](#)