


1

2

3


4

DIMENSIONS



P.C. CARD DRILLING (Component side view)

See drawing ref. C-8609-0000

**FCI**

Copyright FCI.

REV F - 2006-04-17

1

2

3

4

TIN LEAD PART NUMBER

PART NUMBER

86094647824H55113E1

86093967824H55113E1


LEAD FREE PART NUMBER

PART NUMBER

86094647824H55AELF

86093967824H55AELF

ROWS FITTED WITH CONTACTS

ROW a b c ----- 3
ROW a - c ----- 4

SPECIFICATION 113 = 8 grounding pins in position :

or SPECIFICATION AE = row : a-c cavity : 1-2-31-32

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C-8609-0000A

European Views

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection	mm
TOLERANCES UNLESS OTHERWISE SPECIFIED						
Dr	ROUILLARD	2001/01/30	ANGULAR	0.X	± 0.1	size
Eng	TARON	2001/01/30	LINEAR	0.XX	± 0.1	A3 Scale 1.5
Chr	M JACOB	2011/10/21		0.XXX	± 0.1	ECN I11-0176
Appr	BIJU K PAUL	2011/10/21	Product family	DIN 8609	Spec ref	-
FCI			REVERSE MALE 3 ROW 64 CONTACTS			Rev. D
catalog no			dwg no C-8609-0878			customer sheet 1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[86094647824H55AELF](#)