






NOTE-2: ONE CENTER PEG FOR HOLD DOWN FORCE
NOTE-3: CODING RECESS FOR 8MM EXTENDED KEYS
NOTE-4: PRODUCT MARKING = FCI + BATCH CODE + PRODUCT NUMBER
FOR 4 MODULE SIZE, ADD CSA LOGO MARKING
NOTE-6: CENTRAL WALL WITH END REAR SUPPORT
NOTE-7: PACKAGING IN TRAY + COVER
IF SUFFIX "P" IS ADDED IN P/N PACKAGING IS IN TRAYS
BUT CONNECTOR MARKING IS WITHOUT "P"
EXAMPLE: HM1XXXXXXXXXH6P, MARKED HM1XXXXXXXXXH6



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE PRODUCT SPECIFICATION GS-12-446

OTHERS INFORMATIONS, SEE DRW C-8626-0156-2 European Views

rev	ecn no	dr	date
F	-	CHA	2003/07/03
G	LS05-0070	MRA	2005/08/24
H	LS06-0097	LGO	2006/07/13
J	LS07-0184	MLE	2007/07/24
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		✓	tolerance std ISO 406 ISO 1101		projection 	mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	CHAMPION	1994/09/09	ANGULAR	LINEAR	0.X		±0.1	size A3	Scale 2.5	
Eng	TARON	1994/09/09			0.XX		±0.1			
Chr	LEGARE	1994/09/09			0.XXX		±0.1			
Appr	LEGARE	1994/09/09	0.XX' ±2°					ECN LS07-0184		
			Product family				METRAL		Spec ref -	
			title METRAL RA HEADER WB CONVERGED 4x24 CTS - STB - PUSH PEG				no C-8626-0156-1			Rev. J
			catalog no -				CUSTOMER			sheet 1 of 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[HM1L43DDP270H6PLF](#)