


PC board drilling dimensions(after plating)
(thickness ≤ 3.20±0.30mm)






SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	TIN LEAD	TIN LEAD	TIN LEAD	TIN LEAD	LEAD FREE	LEAD FREE	LEAD FREE
09	30.81	24.99	16.96	16.79	10.96	D09P91C4P V00	D09P91C6P V00	D09P91C8P V00	D09P91C4P V00LF	D09P91C6P V00LF	D09P91C8P V00LF	D09P91C8P V00LF
15	39.14	33.32	25.18	25.12	19.18	D15P91C4P V00	D15P91C6P V00	D15P91C8P V00	D15P91C4P V00LF	D15P91C6P V00LF	D15P91C8P V00LF	D15P91C8P V00LF
25	53.03	47.04	39.12	38.84	33.12	D25P91C4P V00	D25P91C6P V00	D25P91C8P V00	D25P91C4P V00LF	D25P91C6P V00LF	D25P91C8P V00LF	D25P91C8P V00LF
37	69.32	63.50	55.68	55.30	49.68	D37P91C4P V00	D37P91C6P V00	D37P91C8P V00	D37P91C4P V00LF	D37P91C6P V00LF	D37P91C8P V00LF	D37P91C8P V00LF
				gold flash			0.76» gold			gold flash		1.25» gold

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0001

European Views

rev	ecn no	dr	date
G	-	MAS	2000/08/24
H	LS05-004	LMA	2004/12/31
J	LS06-0097	LGO	2006/07/29
K	LS06-0140	LGO	2006/09/22
L	109-0268	NG	2009-11-24
-	-	-	-

www.fciconnect.com			surface ISO 1302		✓	tolerance std ISO 406 ISO 1101		projection 	mm 		
TOLERANCES UNLESS OTHERWISE SPECIFIED											
Dr	PESSON	1992-09-15	ANGULAR	LINEAR		0.X	±0.1	size	A3	Scale 2	
Eng	PESSON	1992-09-15				0.XX	±0.1				
Chr	NIRMAL GEORGE	2009-11-24	0.XX' ±2°			0.XXX	±0.1	ECN	109-0268		
Appr	SUDHIR VARMA	2009-11-24	Product family				D-SUB		Spec ref -		
			MALE CONNECTOR DELTA D EUROPE STRAIGHT PRESS-FIT				title		no		Rev.
							dwg		C01-8646-0112		
catalog no			-				CUSTOMER		sheet 1 of 1		



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[D09P91C4PV00LF](#) [D09P91C6PV00LF](#) [D15P91C4PV00LF](#) [D15P91C6PV00LF](#) [D25P91C4PV00LF](#)
[D25P91C6PV00LF](#) [D37P91C4PV00LF](#) [D37P91C6PV00LF](#) [D09P91C4PV00](#) [D09P91C6PV00](#) [D15P91C4PV00](#)
[D15P91C6PV00](#) [D25P91C4PV00](#) [D25P91C6PV00](#) [D37P91C4PV00](#) [D37P91C6PV00](#)