


PC board drilling dimensions(after plating)
(thickness ≤ 3.20±0.30mm)



TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S91C4PA00	D09S91C6PA00
15	39.14	33.32	25.18	24.54	19.18	D15S91C4PA00	D15S91C6PA00
25	53.03	47.04	39.12	38.25	33.12	D25S91C4PA00	D25S91C6PA00
37	69.32	63.50	55.68	54.71	49.68	D37S91C4PA00	D37S91C6PA00
						gold flash	0.76µ gold

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S91C4PA00LF	D09S91C6PA00LF
15	39.14	33.32	25.18	24.54	19.18	D15S91C4PA00LF	D15S91C6PA00LF
25	53.03	47.04	39.12	38.25	33.12	D25S91C4PA00LF	D25S91C6PA00LF
37	69.32	63.50	55.68	54.71	49.68	D37S91C4PA00LF	D37S91C6PA00LF
						gold flash	0.76µ gold

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0001

European Views

www.fciconnect.com		surface ISO 1302	tolerance std ISO 406 ISO 1101	projection mm	size A3		Scale 2
		TOLERANCES UNLESS OTHERWISE SPECIFIED					
Dr	JOUBERT	1995/08/11	ANGULAR	0.X	±0.1		
Eng	PESSON	1995/08/11	LINEAR	0.XX	±0.1		
Chr	LEGARE	1995/08/11	0.XX' ±2'	0.XXX	±0.1		
Appr	LEGARE	1995/08/11	Product family		D-SUB		Spec ref -
				ECN		LS06-0140	
				Title		C01-8646-0127	
				straight press-fit			
				CUSTOMER		sheet 1 of 1	

rev	ecn no	dr	date
F	-	-	1996/07/17
G	LS05-004	MPE	2005/02/07
H	LS06-0095	LGO	2006/06/19
J	LS06-0140	LGO	2006/09/22
-	-	-	-
-	-	-	-
-	-	-	-



FEMALE CONNECTOR DELTA D STD EUROPE

catalog no

dwg no

C01-8646-0127

Rev.
J

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[D09S91C4PA00LF](#) [D09S91C6PA00LF](#) [D15S91C4PA00LF](#) [D15S91C6PA00LF](#) [D25S91C4PA00LF](#)
[D25S91C6PA00LF](#) [D37S91C4PA00LF](#) [D37S91C6PA00LF](#) [D09S91C4PA00](#) [D09S91C6PA00](#) [D15S91C4PA00](#)
[D15S91C6PA00](#) [D25S91C4PA00](#) [D25S91C6PA00](#) [D37S91C4PA00](#) [D37S91C6PA00](#)