






Copyright FCI.

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	TIN LEAD	TIN LEAD	TIN LEAD	LEAD FREE	LEAD FREE	LEAD FREE	LEAD FREE *
						PART NUMBER	PART NUMBER	PART NUMBER	PART NUMBER	PART NUMBER	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S91C4PV00	D09S91C6PV00	D09S91C8PV00	D09S91C4PV00LF	D09S91C6PV00LF	D09S91C8PV00LF	D09S91C4PS00LF
15	39.14	33.32	25.18	24.54	19.18	D15S91C4PV00	D15S91C6PV00	D15S91C8PV00	D15S91C4PV00LF	D15S91C6PV00LF	D15S91C8PV00LF	D15S91C4PS00LF
25	53.03	47.04	39.12	38.25	33.12	D25S91C4PV00	D25S91C6PV00	D25S91C8PV00	D25S91C4PV00LF	D25S91C6PV00LF	D25S91C8PV00LF	D25S91C4PS00LF
37	69.32	63.50	55.68	54.71	49.68	D37S91C4PV00	D37S91C6PV00	D37S91C8PV00	D37S91C4PV00LF	D37S91C6PV00LF	D37S91C8PV00LF	D37S91C4PS00LF
						gold flash	0.76» gold	1.25» gold	gold flash	0.76» gold	1.25» gold	gold flash

NOTE 1

* Part numbers have Female screw with thread M2.6

REV F - 2006-04-17

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 		
TOLERANCES UNLESS OTHERWISE SPECIFIED											
Dr	LELEON	1992/09/16	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2			
Eng	LELEON	1992/09/16			0.XX	±0.1					
Chr	ABHILASH	2009/07/29	0.XX' ±2'		0.XXX	±0.1	ECN		109-0153		
Appr	SUDHIR	2009/07/29	Product family				D-SUB	Spec ref -			
			title FEMALE CONNECTOR DELTA D STD EUROPE STRAIGHT PRESS-FIT				dwg no C01-8646-0130				Rev. F
catalog no			-				CUSTOMER		sheet 1 of 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[D09S91C4PV00LF](#) [D09S91C6PV00LF](#) [D15S91C4PV00LF](#) [D15S91C6PV00LF](#) [D25S91C4PV00LF](#)
[D25S91C6PV00LF](#) [D37S91C4PV00LF](#) [D37S91C6PV00LF](#) [D09S91C4PV00](#) [D09S91C6PV00](#) [D15S91C4PV00](#)
[D15S91C6PV00](#) [D25S91C4PV00](#) [D25S91C6PV00](#) [D37S91C4PV00](#) [D37S91C6PV00](#)