


Shell size	Number of contacts	A ^{+0.76} ₀	B ^{+0.25} ₀	C ±0.12	F ^{+0.13} _{-0.03}	G	K max	L ^{+0.22} ₀	Part number
E	09	30.43	16.79	24.99	4.36	5.90 ^{+0.15} ₀	1.50	0.80	86553113
A	15	38.76	25.12	33.32	4.36	5.90 ^{+0.15} ₀	1.50	0.80	86553114
B	25	52.65	38.84	47.04	4.36	5.70 ^{+0.25} ₀	1.50	0.80	86553115
C	37	68.94	55.30	63.50	4.36	5.70 ^{+0.25} ₀	1.50	1.00	86553116

cadmium plated

rev	ecn no	dr	date
A	-	SJO	2000/09/03
B	LS06-0101	MPE	2006/06/19
C	LS07-0135	MPE	2007/05/11
D	LS09-0006	PCR	2009/01/08
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com		surface ISO 1302	tolerance std ISO 406 ISO 1101	projection A3	mm
		TOLERANCES UNLESS OTHERWISE SPECIFIED		size A3	Scale 3
Dr	JOUBERT	2000/09/03	ANGULAR	0.X	±0.1
Eng	JOUBERT	2000/09/03	LINEAR	0.XX	±0.1
Chr	P.LEGARE	-	0.XX' ±2'	0.XXX	±0.1
Appr	P.LEGARE	-	Product family	D-SUB	Spec ref -
FCI		PINS METRAL CAPS		dwg no	Rev.
		PACKAGING 100 PIECES		C01-8655-1534	D
catalog no		CUSTOMER		sheet 1 of 1	

REV F - 2006-04-17

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[86553113](#) [86553114](#)