


Customer Information Sheet

DRAWING No.: M20-792XX42R IF IN DOUBT - ASK © NOT TO SCALE THIRD ANGLE PROJECTION ALL DIMENSIONS IN mm



COMPONENT SPECIFICATIONS:
MATERIAL:
MOULD = GLASS FILLED PA9T, UL94V-0
CONTACTS = PHOSPHOR BRONZE
FINISH:
0.76-2.03µm NICKEL ALL OVER,
0.015µm MIN GOLD ON CONTACT,
2.03-5.08µm TIN ON TAILS
ELECTRICAL:
CURRENT RATING = 3A
CONTACT RESISTANCE = 20mΩ MAX
INSULATION RESISTANCE = 1000MΩ MIN
VOLTAGE PROOF = 1000V AC FOR ONE MINUTE
MECHANICAL:
INSERTION FORCE = 1.96N MAX PER CONTACT
WITHDRAWAL FORCE = 0.29N MIN PER CONTACT
DURABILITY = 300 CYCLES MIN
ENVIRONMENTAL:
OPERATING TEMPERATURE = -40°C TO +105°C

ORDER CODE:
M20-792XX42R
No. OF CONTACTS PER ROW: 20
02-06, 08, 10

NOTES:
1. FOR TAPE AND REEL DETAILS, SEE SHEET 4.

MGP	5	30.11.21	31219
NAME	ISS.	DATE	CN/CO
APPROVED: MGP			
CHECKED: MR			
DRAWN: M.PERREN			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN
www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.50mm
X.XX = ±0.20mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:
SEE ABOVE
FINISH: SEE ABOVE
S/AREA: mm²

TITLE:
2.54mm PITCH DIL HORIZONTAL SOCKET, SMT TAPE & REEL
DRAWING NUMBER:
M20-792XX42R
SHT 3 OF 4

Customer Information Sheet

DRAWING No.: M20-792XX42R

IF IN DOUBT - ASK

C





NOT TO SCALE

THIRD ANGLE PROJECTION


ALL DIMENSIONS IN mm

TAPE DETAILS FOR
02, 03 & 04 WAYS ONLY

TAPE DETAILS FOR
05, 06, 08 & 10 WAYS ONLY




ORDER CODE:
M20-792XX42R
No. OF CONTACTS PER ROW: _____
02-06, 08, 10



PART No.	DIMENSION					REEL QUANTITY
	DIM 'A'	DIM 'B'	DIM 'C'	DIM 'D'	DIM 'E'	
M20-7920242R	32.00±0.30	14.20±0.15	12.00	16.40	28.40	1000
M20-7920342R			16.00	16.10		750
M20-7920442R				16.70		
M20-7920542R			44.00±0.30	20.20±0.15	24.00	13.60
M20-7920642R	16.00					
M20-7920842R	21.20					
M20-7921042R	26.30	40.40				

REEL DETAILS



- NOTES:
1. PRODUCT IS TAPE AND REELED IN GENERAL ACCORDANCE WITH EIA-481 (ELECTRONIC INDUSTRIES ASSOCIATION).
2. FOR CONNECTOR DETAILS AND SPECIFICATIONS, SEE SHEET 3.

MGP	5	30.11.21	31219
NAME	ISS.	DATE	CN/CO
APPROVED: MGP			
CHECKED: MR			
DRAWN: M.PERREN			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.50mm
X.XX = ±0.20mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:
SEE SHEET 3
FINISH: SEE SHEET 3
S/AREA: mm²

TITLE:
2.54mm PITCH DIL HORIZONTAL SOCKET, SMT TAPE & REEL
DRAWING NUMBER:
M20-792XX42R
SHT 4 OF 4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Harwin:

[M20-7920242R](#) [M20-7920342R](#) [M20-7920442R](#) [M20-7920542R](#) [M20-7920642R](#) [M20-7920842R](#) [M20-7921042R](#)