


Customer Information Sheet


DRAWING No.: M20-890XX05R SHEET 2 OF 2 IF IN DOUBT - ASK (C) NOT TO SCALE THIRD ANGLE PROJECTION ALL DIMENSIONS IN mm





**TAPE DETAILS FOR:
04 WAY**

SPECIFICATION:
MATERIAL:
MOULDING = NYLON 6T UL94V-0, BLACK
CONTACT = BRASS
FINISH:
CONTACT = GOLD FLASH OVER NICKEL
ELECTRICAL:
CURRENT RATING = 3.0A
CONTACT RESISTANCE = $20m\Omega$ MAX
INSULATION RESISTANCE = $5000M\Omega$ MIN
DIELECTRIC STRENGTH = 500V AC FOR ONE MIN
ENVIRONMENTAL:
TEMPERATURE RANGE = $-40^{\circ}C$ TO $+105^{\circ}C$
FOR COMPLETE SPECIFICATION, SEE COMPONENT SPECIFICATION C001XX (LATEST ISSUE).


NOTE:
1. THIS PRODUCT IS TAPE AND REELED IN GENERAL ACCORDANCE WITH EIA-481 (ELECTRONIC INDUSTRIES ASSOCIATION).



**TAPE DETAILS FOR:
05, 06, 09 & 20 WAY**



PART No.	DIM 'A'	DIM 'B'	DIM 'C'	DIM 'D'	DIM 'E'	QUANTITY PER REEL
M20-8900405R	24.0 ± 0.3	13.40 ± 0.30	11.50	10.20 ± 0.30	N/A	600
M20-8900505R		13.15 ± 0.20		13.90 ± 0.20		
M20-8900605R	32.0 ± 0.3	15.54 ± 0.30	14.20	13.50 ± 0.30	28.40	500
M20-8900905R	44.0 ± 0.3	23.00 ± 0.30	20.20		40.40	
M20-8902005R	72.0 ± 0.3	51.20 ± 0.30	34.20	13.80 ± 0.30	68.40	600



FM	5	22.06.18	21364
NAME	ISS.	DATE	C/NOTE
APPROVED:	F.MCGOWAN		
CHECKED:	S.BENNETT		
DRAWN:	S.BENNETT		
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN
www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = $\pm 1mm$
X.X = $\pm 0.50mm$
X.XX = $\pm 0.10mm$
X.XXX = $\pm 0.01mm$
ANGLES = $\pm 5^{\circ}$
UNLESS STATED

MATERIAL:
SEE ABOVE
FINISH: SEE ABOVE
S/AREA: mm²

TITLE:
SIL HORIZONTAL SMT
HEADER IN TAPE AND REEL
DRAWING NUMBER:
M20-890XX05R
SHT
2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Harwin:](#)

[M20-8900405R](#) [M20-8900905R](#) [M20-8900605R](#) [M20-8900505R](#)