

# Customer Information Sheet

DRAWING No.: M22-636XXXXR

IF IN DOUBT - ASK


©

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

TAPE DETAILS FOR  
03, 04, 05, 06 AND 07 CONTACTS PER ROW



- NOTES:
- 1. FOR CONNECTOR DETAILS SEE M22-636XXXX.
  - 2. QUANTITY OF COMPONENTS PER REEL = 1200.
  - 3. PICK & PLACE CAP LOCATED CENTRALLY ON COMPONENT.

ORDER CODE: **M22-636XXXXR**


No. OF CONTACTS PER ROW: \_\_\_\_\_  
03, 04, 05, 06, 07,  
10, 12, 17, 21

FINISH: \_\_\_\_\_  
42 - SELECTIVE GOLD FLASH & 100% TIN  
46 - 100% TIN

**OBSOLETE**  
All other size/finish  
combinations not  
listed above


| PART No.     | DIM 'A'    | DIM 'B'    | DIM 'C' | DIM 'D' | DIM 'E' |
|--------------|------------|------------|---------|---------|---------|
| M22-63603XXR | 16.00±0.30 | 7.50       | 6.40    | N/A     | 4.40    |
| M22-63604XXR |            |            | 8.40    |         | 4.60    |
| M22-63605XXR |            |            | 10.40   |         | 4.60    |
| M22-63606XXR | 24.00±0.30 | 11.50      | 12.40   | N/A     | 4.50    |
| M22-63607XXR |            |            | 14.40   |         | 4.50    |
| M22-63610XXR | 32.00±0.30 | 14.20±0.15 | 20.40   | 28.40   | 4.60    |
| M22-63612XXR |            |            | 24.40   |         | 4.60    |
| M22-63617XXR |            |            | 32.90   |         | 4.50    |
| M22-63621XXR | 56.00±0.30 | 26.20±0.15 | 42.40   | 52.40   | 4.60    |

TAPE DETAILS FOR 10,  
12, 17 & 21 CONTACTS PER ROW




Active  
products:


M22-6360442R  
M22-6360542R  
M22-6361042R  
M22-6361242R  
M22-6361742R  
M22-6362142R




DETAIL 'A'



REEL DETAILS



SECTION X-X



FINISHED REELING DIRECTION

|                     |      |          |       |
|---------------------|------|----------|-------|
| MGP                 | 13   | 22.12.21 | 31219 |
| NAME                | ISS. | DATE     | CN/CO |
| APPROVED: MGP       |      |          |       |
| CHECKED: MR         |      |          |       |
| DRAWN: W. J. BOURNE |      |          |       |
| CUSTOMER REF.:      |      |          |       |
| ASSEMBLY DRG:       |      |          |       |

**HARWIN**

www.harwin.com  
technical@harwin.com

THIS DRAWING AND ANY  
INFORMATION OR DESCRIPTIVE  
MATTER SET OUT HEREON ARE  
CONFIDENTIAL AND COPYRIGHT  
PROPERTY OF THE HARWIN  
GROUP AND MUST NOT BE  
DISCLOSED, LOANED, COPIED  
OR USED FOR MANUFACTURING,  
TENDERING OR FOR ANY  
OTHER PURPOSE WITHOUT  
THEIR WRITTEN PERMISSION.

TOLERANCES  
X. = ±1mm  
X.X = ±0.50mm  
X.XX = ±0.20mm  
X.XXX = ±0.01mm  
ANGLES = ±5°  
UNLESS STATED

MATERIAL:

SEE NOTE 1

FINISH: SEE NOTE 1

S/AREA:

mm<sup>2</sup>

TITLE: 2mm PITCH DIL SMT  
VERTICAL LOW-PROFILE SOCKET  
(TAPE AND REEL)

DRAWING NUMBER:

**M22-636XXXXR**

SHT  
3  
OF  
3

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Harwin:](#)

[M22-6360746R](#) [M22-6360442R](#) [M22-6360542R](#) [M22-6360646R](#) [M22-6361742R](#) [M22-6361242R](#) [M22-6361042R](#)