




HARWIN

HARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.com

HARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.uk

HARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sg

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:
SEE NOTES
FINISH:
SEE NOTES
S/AREA:
mm?

TITLE:
M402 V SERIES 0.5 BOARD TO BOARD
SMT V/T TYPE FEMALE
DRAWING NUMBER:
M402VF-3- XXX - XX NR
SHT
1
OF
3

TOTAL NO. OF WAYS \ TYPE	01	02	03	04	05	06	07	08	09	0A	0B
10	●	●	●	⊗	●	⊗	●	⊗	⊗	⊗	⊗
12	⊗	●	●	●	●	●	⊗	⊗	⊗	⊗	⊗
14	●	●	●	●	●	⊗	⊗	⊗	⊗	⊗	⊗
16	●	●	●	●	●	●	⊗	⊗	⊗	⊗	⊗
18	⊗	⊗	●	●	●	●	●	⊗	⊗	⊗	⊗
20	●	●	●	●	●	●	●	⊗	⊗	⊗	⊗
22	●	●	●	⊗	●	●	●	⊗	⊗	⊗	⊗
24	●	●	●	●	●	●	●	⊗	⊗	⊗	⊗
26	●	●	●	●	●	●	●	⊗	⊗	⊗	⊗
28	⊗	⊗	●	●	●	●	●	⊗	⊗	⊗	⊗
30	●	●	●	●	●	●	●	⊗	⊗	⊗	⊗
32	●	⊗	●	●	●	●	●	⊗	⊗	⊗	⊗
34	●	●	●	●	●	⊗	●	⊗	⊗	⊗	⊗
36	●	⊗	●	●	⊗	⊗	●	⊗	⊗	⊗	⊗
38	⊗	⊗	●	●	●	⊗	●	⊗	⊗	⊗	⊗
40	●	●	●	●	●	●	●	⊗	⊗	⊗	⊗
42	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗

TOTAL NO. OF WAYS \ TYPE	01	02	03	04	05	06	07	08	09	0A	0B
44	●	⊗	●	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
46	⊗	⊗	●	⊗	●	⊗	⊗	⊗	⊗	⊗	⊗
48	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
50	●	●	●	●	●	●	●	⊗	⊗	⊗	⊗
52	⊗	⊗	●	⊗	●	⊗	⊗	⊗	⊗	⊗	⊗
54	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
56	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
58	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
60	●	●	●	●	●	●	●	⊗	⊗	⊗	⊗
62	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
64	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
66	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
68	⊗	⊗	⊗	⊗	●	⊗	⊗	⊗	⊗	⊗	⊗
70	⊗	⊗	●	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
72	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
74	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
76	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗

TOTAL NO. OF WAYS \ TYPE	01	02	03	04	05	06	07	08	09	0A	0B
78	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
80	●	●	●	●	●	⊗	⊗	⊗	⊗	⊗	⊗
82	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
84	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
86	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
88	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
90	⊗	⊗	⊗	⊗	⊗	●	⊗	⊗	⊗	⊗	⊗
92	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
94	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
96	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
98	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
100	⊗	⊗	⊗	⊗	●	⊗	⊗	⊗	⊗	⊗	⊗
110	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
120	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
130	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
140	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
150	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗
160	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗	⊗

OBSOLETE
from
31-01-2019:
M402VF-3-038-05NR



- - MOULDS AVAILABLE
- - MOULDS UPON REQUEST.
PLEASE REFER TECHNICAL SALES
- ✕ - OBSOLETE ITEMS

Leo	14	01.04.16	A481
Leo	13	01.03.16	A477
MSP	12	18.11.14	12694
Allan	11	02.09.09	A232
Allan	10	21.08.09	A231
Allan	9	06.08.09	A227
Allan	8	31.07.08	A150


NAME	ISS.	DATE	C/NOTE
APPROVED:		B.Lim	
CHECKED:		D.P	
DRAWN:		Leo	
CUSTOMER REF.:			
ASSEMBLY DRG:			

NOTES: ALL DIMENSIONS AND NOTES
MARKED ✕ ARE CRITICAL AND
MUST BE CHECKED IN ACCORDANCE
WITH QUALITY DOC. Q1-02A

ORDER CODE
M402VF-3- XXX - XX NR
TOTAL NO. OF WAYS $\prod$ TYPE
(REFER TO TABLE)



SECTION A-A



SECTION B-B


W	W1	W2
16		7.50
24		11.50
32	28.40	14.20
44	40.40	20.20
56	52.40	26.20
72	68.40	34.20

CKT	10	14	18	22	26	30	34	38	42	46
PIN	10 12	14 16	18 20	22 24	26 28	30 32	34 36	38 40	42 44	46 48
W	016	016	024	024	024	024	024	024	024	032
B0	7.90	8.90	9.90	10.90	11.90	12.90	13.90	14.90	15.90	16.90

CKT	50	54	58	62	66	70	74	78	82	86
PIN	50 52	54 56	58 60	62 64	66 68	70 72	74 76	78 80	82 84	86 88
W	032	032	032	044	044	044	044	044	044	044
B0	17.90	18.90	19.90	20.90	21.90	22.90	23.90	24.90	25.90	26.90

CKT	90	94	98	B0	C0	D0	E0	F0	G0
PIN	90 92	94 96	98 A0	B0	C0	D0	E0	F0	G0
W	044	044	044	056	056	056	056	056	072
B0	27.90	28.90	29.90	32.40	34.90	37.90	49.90	42.40	44.90

ITEM	A0	A1	K0	K1	PITCH	PCS/REEL
DIM	5.10	6.50	4.20	4.80	12.00	1200



NOTES: ALL DIMENSIONS AND NOTES MARKED * ARE CRITICAL AND MUST BE CHECKED IN ACCORDANCE WITH QUALITY DOC. Q1-02A

Leo	14	01.04.16	A481
Leo	13	01.03.16	A477
MSP	12	18.11.14	12694
Allan	11	02.09.09	A232
Allan	10	21.08.09	A231
Allan	9	06.08.09	A227
Allan	8	31.07.08	A150

NAME	ISS.	DATE	C/NOTE
------	------	------	--------

APPROVED: B.Lim

CHECKED: D.P


DRAWN: Leo

CUSTOMER REF.:

ASSEMBLY DRG:

NOTES:

1. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE ± 0.20
2. CARRIER CAMBER IS WITHIN 1MM IN 250MM
3. MATERIAL: BLACK CONDUCTIVE POLYSTYRENE ALLOY



HARWIN

HARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.com

HARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.uk

HARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sg

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES

X. = $\pm 1\text{mm}$
X.X = $\pm 0.20\text{mm}$
X.XX = $\pm 0.10\text{mm}$
X.XXX = $\pm 0.01\text{mm}$

ANGLES = $\pm 0'30''$
UNLESS STATED

MATERIAL:

SEE NOTES

FINISH:

SEE NOTES

S/AREA:

mm?

TITLE:

M402V SERIES 0.5 BOARD TO BOARD
SMT V/T TYPE FEMALE

DRAWING NUMBER:

M402VF-3- XXX - XX NR

SHT
3
OF
3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Harwin:

[M402VF-3-010-03NR](#) [M402VF-3-032-06NR](#) [M402VF-3-034-07NR](#) [M402VF-3-030-05NR](#) [M402VF-3-040-05NR](#)
[M402VF-3-040-06NR](#) [M402VF-3-080-03NR](#) [M402VF-3-020-05NR](#) [M402VF-3-016-02NR](#) [M402VF-3-038-05NR](#)