



Recommended PCB Layout

SPECIFICATIONS:

MATERIAL:-

MOULDING: PBT G.F. UL94V-0, WHITE

CONTACT: PHOSPHOR BRONZE, T=0.25

FINISH:-

SELECTIVE GOLD

ELECTRICAL:-

CURRENT RATING: 1.5 AMP

WORKING VOLTAGE: 30V AC/DC

WITHSTANDING VOLTAGE: 500V AC/MINUTE

CONTACT RESISTANCE: 30 mΩ MAX.

INSULATION RESISTANCE: 1000 MΩ MIN.

MECHANICAL:-

DURABILITY: 1500 CYCLES MIN.

MATING FORCE: 35N MAX.

WITHDRAWAL FORCE: 10N MIN.

ENVIRONMENTAL:-

TEMPERATURE RANGE: -55°C TO +85°C

Leo	4	28.10.15	A471
Leo	3	02.10.15	A468
Allan	2	16.07.09	A220
Allan	1	01.08.06	--

NAME	ISS.	DATE	C/NOTE
------	------	------	--------

APPROVED: B.Lim

CHECKED: D.P

DRAWN: Leo

CUSTOMER REF.:

ASSEMBLY DRG:

NOTES: ALL DIMENSIONS AND NOTES
MARKED ✕ ARE CRITICAL AND
MUST BE CHECKED IN ACCORDANCE
WITH QUALITY DOC. QI-02A

HARWIN

HARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.com

HARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.uk

HARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sg

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES
LINEAR
X.X = ±0.38mm
X.XX = ±0.25mm
X.XXX = ±0.13mm
ANGLES
X.X = ±2°
X.XX = ±1°
X.XXX = ±0.5°
UNLESS STATED

MATERIAL:

SEE NOTES

FINISH:

SEE NOTES

S/AREA:

mm?

TITLE:

USB B TYPE FEMALE DIP 180°

DRAWING NUMBER:

M701-330442

SHT
1
OF
1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Harwin:

[M701-330442](#)