




Customer Information Sheet

DRAWING No.: M80-904XX02 IF IN DOUBT - ASK © NOT TO SCALE THIRD ANGLE PROJECTION ALL DIMENSIONS IN mm



- NOTES:
1. ALL PCB LAYOUTS DRAWN WITH MATING FACE BELOW PINS/PADS. LAYOUTS ONLY FOR BACKSHELL MOUNTING, FOR CONNECTOR PCB LAYOUT SEE COMPONENT DRAWING.
 2. MAXIMUM DISTANCE FROM EDGE OF BOARD WHEN PAIRING WITH SHIELDED CABLE.
 3. MOUNTING HARDWARE NOT PROVIDED, M2 FIXINGS WITH 4.5mm MAX BOLT HEAD DIAMETER RECOMMENDED. BOLT FROM ABOVE.

DIMENSION	CALCULATION
DIM 'A'	TOTAL No. OF CONTACTS - 2
DIM 'B'	TOTAL No. OF CONTACTS - 2
DIM 'C'	TOTAL No. OF CONTACTS + 16.3

ORDER CODE: **M80-904XX02**

TOTAL No. OF CONTACTS _____

04 - 50
EVEN NUMBERS ONLY

RA	2	15.06.21	30584
NAME	ISS.	DATE	CN/CO
APPROVED: R.ALEXANDER			
CHECKED: M.RUDKIN			
DRAWN: R.ALEXANDER			
CUSTOMER REF.:			
ASSEMBLY DRG:			

SPECIFICATIONS:

MATERIAL = ALUMINIUM ALLOY

FINISH = ELECTROLESS NICKEL

ENVIRONMENTAL:

TEMPERATURE RANGE = -55°C TO +125°C

HARWIN

www.harwin.com

technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES

X. = ±1mm

X.X = ±0.50mm

X.XX = ±0.20mm

X.XXX = ±0.01mm

ANGLES = ±5°

UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²

TITLE:

DATAMATE J-TEK MALE HORIZONTAL SMT BOARD MOUNT BACKSHELL

DRAWING NUMBER:

M80-904XX02

SHT 5 OF 5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Harwin:

[M80-9040402](#) [M80-9040602](#) [M80-9040802](#) [M80-9041002](#) [M80-9041202](#) [M80-9045002](#) [M80-9043802](#) [M80-9044002](#) [M80-9044202](#) [M80-9044402](#) [M80-9044602](#) [M80-9044802](#) [M80-9042602](#) [M80-9042802](#) [M80-9043002](#) [M80-9043202](#) [M80-9043402](#) [M80-9043602](#) [M80-9041402](#) [M80-9041602](#) [M80-9041802](#) [M80-9042002](#) [M80-9042202](#) [M80-9042402](#)