

HEYCO

Heyco®-Tite Brass Liquid Tight Cordgrips, Metric Hubs

Explosion Proof for Hazardous Locations


The Ultimate in Liquid Tight Strain Relief Protection

**ALL NEW
PRODUCTS!**



Cable Diameter Range				Part No.	Thread Size	Part Dimensions							
Minimum		Maximum				A Clearance Hole Dia.		B Max. O.A. Length		C Thread Length		D Wrenching Flat Size	
in.	mm.	in.	mm.			in.	mm.	in.	mm.	in.	mm.	in.	mm.
.118	3,0	.276	7,0	14830	M16 x 1,5	.630	16,0	1.50	38,0	.47	12,0	.83	21,0
.197	5,0	.394	10,0	14831		.630	16,0	1.50	38,0	.47	12,0	.94	24,0
.197	5,0	.433	11,0	14832	M20 x 1,5	.787	20,0	1.50	38,0	.47	12,0	.94	24,0
.354	9,0	.551	14,0	14833		.787	20,0	1.50	38,0	.47	12,0	1.18	30,0
.295	7,5	.591	15,0	14834	M25 x 1,5	.984	25,0	1.57	40,0	.47	12,0	1.26	32,0
.492	12,5	.709	18,0	14835		.984	25,0	1.57	40,0	.47	12,0	1.26	32,0
.669	17,0	.906	23,0	14836	M32 x 1,5	1.260	32,0	1.77	45,0	.47	12,0	1.61	41,0
.827	21,0	1.024	26,0	14837		1.260	32,0	1.77	45,0	.47	12,0	1.61	41,0
.827	21,0	1.024	26,0	14838	M40 x 1,5	1.575	40,0	1.85	47,0	.55	14,0	1.61	41,0
.945	24,0	1.260	32,0	14839		1.575	40,0	1.89	48,0	.55	14,0	1.97	50,0
1.102	28,0	1.417	36,0	14840	M50 x 1,5	1.968	50,0	1.89	48,0	.55	14,0	2.17	55,0
1.378	35,0	1.654	42,0	14841		1.968	50,0	1.93	49,0	.55	14,0	2.36	60,0
1.417	36,0	1.732	44,0	14842	M63 x 1,5	2.480	63,0	1.93	49,0	.55	14,0	2.56	65,0
1.693	43,0	1.968	50,0	14843		2.480	63,0	1.93	49,0	.55	14,0	2.76	70,0

- Suitable for flameproof enclosures Ex d 11C and increased safety Ex e 11
- Certificate: EC-type examination certificate PTB 10 ATEX 1034X
- Certificate: IECEx Certificate: IECEx PTB 12.0055x
- Certified for category 2G: II 2G Ex db eb IIC
- Certified for category 2D: II 2D Ex ta IIIC
- Zone: Gas 1 and 2/dust 21 and 22



Cordgrips

Locking Plugs

Heyco®-Tite Brass Locking Plugs, Metric Hubs

THREAD TYPE / SIZE	PART NO.	DESCRIPTION	PART DIMENSIONS			
			A Wrenching Flats		B Overall Length	
			in.	mm.	in.	mm.
M12 x 1,5	14691	BRASS TPX M12	.59	15,0	.79	20,0
M16 x 1,5	14692	BRASS TPX M16	.71	18,0	.83	21,0
M20 x 1,5	14693	BRASS TPX M20	.94	24,0	.91	23,0
M25 x 1,5	14694	BRASS TPX M25	1.18	30,0	.98	25,0
M32 x 1,5	14695	BRASS TPX M32	1.42	36,0	1.06	27,0
M40 x 1,5	14696	BRASS TPX M40	1.81	46,0		
M50 x 1,5	14697	BRASS TPX M50	2.17	55,0		
M63 x 1,5	14698	BRASS TPX M63	2.76	70,0		

- Suitable for flameproof enclosures Ex d IIC
- IECEx Certificate: 1ECEx PTB 12.0056
- Certified for category 2G: II 2G Ex db eb IIC
- Certified for category 2D: II 2D Ex ta IIIC
- Zone: Gas 1 and 2/dust 21 and 22



Material
Temperature Range
IP Rating

Cordgrips
Nickel-Plated Brass Body w/NBR Seal
-76°F (-60°C) to 221°F (105°C)
IP 68, IP 69K

Locking Plugs
Nickel-Plated Brass Body w/FPM O-Ring
-40°F (-40°C) to 212°F (100°C)
IP 69K

*Quick
Specs*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[14843](#) [14836](#) [14692](#) [14834](#) [14841](#) [14833](#) [14696](#) [14838](#) [14831](#) [14842](#) [14830](#) [14832](#) [14694](#) [14697](#) [14695](#)
[14837](#) [14840](#) [14698](#) [14839](#) [14835](#) [14691](#)