


HEYCO

Heyco® Nylon D-Subminiature Mounting Hole Plugs

Clearance Fit for Panel Thickness up to .170" (4,3 mm)

MOUNTING HOLE SIZE				PART NO.	DESCRIPTION	PART DIMENSIONS							
A		B				C	D		E		F		
in.	mm.	in.	mm.				Head	in.	mm.	in.	mm.	Body	in.
.45	11,4	.81	20,6	2966	POP-DB9	1.25	31,8	.70	17,8	.69	17,5	.41	10,4
		1.13	28,8	2968	POP-DB15	1.57	39,8	.70	17,8	1.05	26,7		
		1.67	42,5	2970	POP-DB25	2.12	51,0	.70	17,8	1.55	39,4		
		2.32	59,1	2972	POP-DB37	2.77	70,4	.70	17,8	2.23	56,6		

Standard color black. Consult Heyco for other colors.



Material	Nylon 6/6
Certifications	<p>Recognized under the Component Program of Underwriters' Laboratories, File E51579</p> <p>Certified by Canadian Standards Association, File 8919</p>
Flammability Rating	94V-2
Temperature Range	-40°F (-40°C) to 221°F (105°C)



- Fit standard D-Subminiature Cutouts.
- Provide aesthetic improvement for unused D-subminiature connector mounting holes.
- Suitable for use as dust protection for unused parallel and serial ports on computers and other electrical equipment.
- Cover unwanted holes in panel and are easily removable.
- Quick and easy installation with fingertip pressure.

Custom Color Match
and Special Engraved
Identification Available.
Consult Heyco for
Details

*Quick
Specs*




Heyco® IEC-14 Plug

For IEC-13 Female Connectors

PART NO. Black	DESCRIPTION	PART DIMENSIONS					
		A		B		C	
		in.	mm.	in.	mm.	in.	mm.
G5365	IECP C14	.96	24,4	.66	16,8	.38	9,7

Standard color black.



- These non-conductive plugs are used to **protect female IEC-13 connectors** during transit and storage.
- Will keep your connector **free of dust, moisture, and contaminants**.
- The flanged Plug head provides **ease of installation and removal**.
- Consult Heyco for the **IEC-20 Plug** (for IEC-19 female connectors).

Material	LDPE
Temperature Range	-94°F (-70°C) to 150°F (66°C)

*Quick
Specs*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[2966](#) [2968](#) [2970](#) [2972](#) [G5365](#)