




HEYClip™ Split Dart Cable Holders

MAXIMUM BUNDLE DIA.		MOUNTING HOLE DIA.		PART NO. Natural	DESCRIPTION	OVERALL HEIGHT C		STYLE
in.	mm.	in.	mm.			in.	mm.	
For panels up to .047" (1,2 mm) thick								
.150	3,8	.256	6,5	12379	CH SD-38-65	.35	8,9	1
For panels up to .063" (1,6 mm) thick								
.114	2,9	.177	4,5	12387	CH SD-29-45	.25	6,4	2
.150	3,8	.256	6,5	12386	CH SD-38-65-1	.35	8,9	1
.331	8,4	.217	5,5	12380	CH SD-84-55	.43	10,9	3
		.236	6,0	12381	CH SD-84-60	.47	11,9	
For panels up to .075" (1,9 mm) thick								
.437	11,1	.236	6,0	12382	CH SD-111-60	.55	14,0	3
For panels from .079" (2,0 mm) thick								
.197	5,0	.256	6,5	12383	CH SD-50-65	.32	8,1	3
.217	5,5	.217	5,5	12384	CH SD-55-55	.31	7,9	
.295	7,5	.217	5,5	12385	CH SD-75-55	.38	9,7	

Standard color natural.




- Split dart feature allows user to easily slip the cable holder over the cable which is held firmly in place once inserted into the mounting hole.
- Designed to hold a single cable or wire bundles.


HEYClip™ Optical Fiber Network Cable Holders

WIRE CAPACITY		MOUNTING HOLE DIAMETER		DART STYLE	PART NO. Natural		DESCRIPTION	OVERALL HEIGHT C		FOOTPRINT A x B	
in.	mm.	in.	mm.		94V-2	94V-0		in.	mm.	in.	mm.
For Round Mounting Holes For panels from .031" (0,8 mm) to .079" (2,0 mm) thick											
.83 x .75	21,1 x 19,1	.187	4,8	1	12150	12150F	CH OF-282-48	1.25	31,8	.27 x 1.06	6,9 x 26,9
		.250	6,4	2	12151	12151F	CH OF-282-64				
1.13 x .99	28,7 x 25,1	.187	4,8	1	12153	12153F	CH OF-344-48	1.50	38,1	.27 x 1.35	6,9 x 34,3
		.250	6,4	2	12154	12154F	CH OF-344-64				
For Square Mounting Holes For panels from .031" (0,8 mm) to .079" (2,0 mm) thick											
.83 x .75	21,1 x 19,1	.374	9,5	4	12156	12156F	CH OF-282-95S	1.19	30,2	.27 x 1.06	6,9 x 26,9
1.13 x .99	28,7 x 25,1	.307	7,8	3	12161	12161F	CH OF-344-78S	1.44	36,6	.27 x 1.35	6,9 x 34,3
		.374	9,5	4	12157	12157F	CH OF-344-95S				
1.38 x 1.73	35,1 x 43,9	.374	9,5	4	12158	12158F	CH OF-550-95S	2.25	57,2	.27 x 1.69	6,9 x 42,9


Standard color natural.




Style 1



Style 2



Style 3



Style 4

	Split Dart	Optical Fiber
Material	Nylon 6/6	Nylon 6/6
Flammability Rating	94V-2	94V-2 and 94V-0
Temperature Range	-40°F (-40°C) to 185°F (85°C)	32°F (0°C) to 185°F (85°C) (94V-2) 32°F (0°C) to 203°F (95°C) (94V-0)

*Quick
Specs*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[8948](#) [8941](#)