


**ALL NEW
PRODUCTS!**

Heyco® Nytye® Heavy Duty and Extra Heavy Duty/HVAC Nylon Cable Ties

PART SPECIFICATIONS				PART NO.		DESCRIPTION	PART DIMENSIONS			
Max. Tensile Strength		Max. Bundle Diameter		Natural	UV Black		A Length		B Width	
Lbs.	N	in.	mm.				in.	mm.	in.	mm.
Heavy Duty										
120	534	1.30	33,0	13172	13172B	NT-120-059	5.91	150	.30	7,6
		1.97	50,0	13175	13175B	NT-120-078	7.87	200		
		2.48	63,0	13178	13178B	NT-120-098	9.84	250		
		3.23	82,0	13181	13181B	NT-120-118	11.81	300		
		3.54	90,0	13183	13183B	NT-120-137	13.78	350		
		3.98	101,0	13185	13185B	NT-120-149	14.96	380		
		4.13	105,0	13186	13186B	NT-120-157	15.75	400		
Extra Heavy Duty/HVAC										
175	778	.39	10,0	13208	13208B	NT-175-255	25.59	650	.35	9,0
				13215	13215B	NT-175-315	31.50	800		
				13217	13217B	NT-175-354	35.43	900		
				13218	13218B	NT-175-393	39.37	1000		
				13220	13220B	NT-175-477	47.76	1213		

Standard colors natural and UV Black. Consult Heyco for heat-stabilized material and colors.

- Smooth, radiused edges ensure that Nytyes won't cut into the cable's insulation—or the installer's hand.
- One-piece design reduces cost and installation time.
- Nytyes feature a bent tip for ease of pickup and insertion around small bundles. V-shaped raised ridges on the tip provide a sure grip.
- Close, evenly spaced teeth permit fine adjustment—from .025" (0,6 mm) on the smallest Nytyes to .063" (1,6 mm) on the largest.
- Compliant with MS3367 and MIL-S-23190E



Material
Certifications



Nylon 6/6
Certified by UL for Compliance with both Canadian and U.S. requirements under File E54523

Flammability Rating
Temperature Range

94V-2
-40°F (-40°C) to 185°F (85°C)

*Quick
Specs*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[13208B](#) [13220B](#) [13215B](#) [13218B](#) [13217B](#) [13183](#) [13186](#) [13186B](#) [13175](#) [13178](#) [13172](#) [13185](#) [13185B](#) [13220](#)
[13175B](#) [13178B](#) [13215](#) [13172B](#) [13208](#) [13183B](#) [13217](#) [13218](#) [13181B](#)