





Heyco® Nytye® Heavy Duty and Extra Heavy Duty/HVAC Nylon Cable Ties

PART SPECIFICATIONS				PART NO.		DESCRIPTION	PART DIMENSIONS			
Tensile Strength		Max. Bundle Diameter		Natural	UV Black		A Length		B Width	
Lbs.	N	in.	mm.				in.	mm.	in.	mm.
Heavy Duty										
120	534	1.30	33,0	13172	13172B	NT-120-059	5.91	150	.30	7,6
		1.97	50,0	13175	13175B	NT-120-078	7.87	200		
		2.48	63,0	13178	13178B	NT-120-098	9.84	250		
		3.23	82,0	13181	13181B	NT-120-118	11.81	300		
		3.54	90,0	13183	13183B	NT-120-137	13.78	350		
		3.98	101,0	13185	13185B	NT-120-149	14.96	380		
		4.13	105,0	13186	13186B	NT-120-157	15.75	400		
	6.10	155,0	13190	13190B	NT-120-216	21.65	550			
Extra Heavy Duty/HVAC										
175	778	7.48	190,0	13208	13208B	NT-175-256	25.59	650	.35	9,0
		9.65	245,0	13215	13215B	NT-175-315	31.50	800		
		10.67	271,0	13217	13217B	NT-175-362	36.22	920		
		11.42	290,0	13218	13218B	NT-175-394	39.37	1000		
		14.49	368,0	13220	13220B	NT-175-482	48.23	1225		



Standard colors natural and UV Black. Consult Heyco for heat-stabilized material and colors.



Heyco® Nytye® Double Loop Cable Ties

PART SPECIFICATIONS				PART NO. Natural	DESCRIPTION	PART DIMENSIONS			
Tensile Strength		Max. Combined Bundle Diameter F				A Length		B Width	
Lbs.	N	in.	mm.			in.	mm.	in.	mm.
50	222	1.77	45,0	13320	NTDL-050-076	7.68	195	.19	4,8
		2.05	52,0	13321	NTDL-050-088	8.86	225		
		2.99	76,0	13323	NTDL-050-118	11.81	300		
		3.86	98,0	13324	NTDL-050-145	14.56	370		

Standard color natural.



Material
Certifications



Nylon 6/6
Certified by UL for Compliance with both Canadian and U.S. requirements under File E54523 (NT parts only)

Flammability Rating
Temperature Range

94V-2
-40°F (-40°C) to 185°F (85°C)

Quick
Specs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[13321](#) [13324](#) [13320](#) [13323](#)