



## HEYClean® Brass Pressure Equalization and Drain Plugs

For Pressure Equalization and Drainage Applications

THREAD	PART NO.		DESCRIPTION	PART DIMENSIONS								PROTECTION CLASS
Type/Size	STD.	EXP*		A Clearance Hole		B Overall Length		C Thread Length		D Wrenching Flats		
		<b>NEW</b>		in.	mm.	in.	mm.	in.	mm.	in.	mm.	

### Liquid Tight Pressure Equalization Plugs – Ultimate in Liquid Tight Pressure Equalization

M12 x 1.5	<b>4350</b>	<b>14350</b>	BRASS LTPEP M12	.47	12,0	.69	17,5	.31	8,0	.71	18,0	IP 66,67,68
M16 x 1.5	<b>4351</b>	<b>14351</b>	BRASS LTPEP M16	.63	16,0							
M20 x 1.5	<b>4352</b>	<b>14352</b>	BRASS LTPEP M20	.79	20,0	.71	18,0	.31	8,0	.87	22,0	

### Liquid Resistant Pressure Equalization Plugs – Maximize Airflow for Extreme Pressure and Moisture Fluctuations

M12 x 1.5	<b>4354</b>	–	BRASS LRPEP M12	.47	12,0	.69	17,5	.31	8,0	.71	18,0	IP 55, x9K
M16 x 1.5	<b>4355</b>	–	BRASS LRPEP M16	.63	16,0							
M20 x 1.5	<b>4356</b>	–	BRASS LRPEP M20	.79	20,0	.71	18,0	.31	8,0	.87	22,0	


### Threaded Drain Plug – For Applications Where Condensation Is Expected\*\*

M12 x 1.5	<b>4357</b>	–	BRASS TDP M12	.47	12,0	.77	19,5	.39	10,0	.71	18,0	IP 4x
M16 x 1.5	<b>4358</b>	–	BRASS TDP M16	.63	16,0							
M20 x 1.5	<b>4359</b>	–	BRASS TDP M20	.79	20,0	.79	20,0	.39	10,0	.87	22,0	

Stainless Steel available. Consult Heyco.

\*Certified in accordance with IECEx and ATEX


\*\*Heyco Drainage Plug Brass Locknuts sold separately



## HEYClean® Drain Plug Brass Locknuts

For Use with HEYClean™ Threaded Drain Plugs

THREAD	PART NO.	DESCRIPTION	PART DIMENSIONS			
Type/Size			A Thickness		B Wrenching Flats	
			in.	mm.	in.	mm.
M12 x 1.5	<b>4360</b>	BRASS DPLN M12	.18	4,5	.59	15,0
M16 x 1.5	<b>4361</b>	BRASS DPLN M16	.22	5,5	.75	19,0
M20 x 1.5	<b>4362</b>	BRASS DPLN M20	.22	5,5	.94	24,0



Material	Nickel-Plated Brass
Temperature Range	-40°F (-40°C) to 230°F (110°C)
IP Rating	Membrane - IP66/IP68/IP69 Filter Disc - IP55/ IPX9K Drainage Element - IP4X

### Pressure Equalization Plugs

- Allow the passage of air for ventilation and heat dissipation, yet prevent moisture intrusion.
- Filter membrane prevents moisture and particulate contamination in electronic enclosures.
- Pressure compensating seal prevents buildup of pressure inside of electronic enclosures due to environmental temperature cycling.
- Quick and easy installation into Clearance or Threaded Holes.
- **Nickel-plated finish over brass provides excellent corrosion resistance and durability.**
- Head Thickness: .37" (9,5 mm) to .39" (10 mm).
- Hex shaped body for wrench installation.
- Filter element:  
Liquid Tight Membrane: Polyethersulfone (PES)  
Sintered Disc: Bronze
- DFARS Compliant

### Drain Plugs

- Drainage Plugs are ideal for applications where condensation is expected.
  - Stainless steel mesh allows water to drain quickly, but protects enclosure from bugs and dust.
  - Drainage Plugs feature a "cutout" section to allow water to completely drain from enclosure, and should be installed at enclosure's lowest point.
  - Head Thickness: .37" (9,5 mm) to .39" (10 mm).
  - Hex shaped body for wrench installation.
  - DFARS Compliant
- ### Drain Plug Locknuts
- Quick and easy installation into Clearance Holes only.
  - Locknuts feature special "cutout" to allow water to completely drain from enclosure, when used with HEYClean™ Threaded Drain Plugs.
  - DFARS Compliant

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[4360](#) [4361](#) [4362](#)