




Heyco® Original Strain Relief Bushings

Straight-Thru for Round Cables

.375" (9,5 mm) to .500" (12,7 mm) Mounting Holes

- **Protects the lifeline of your electric/electronic products** by absorbing the forces of pull, push, and twist that maybe exerted on the flexible power cord.
- Securely anchors, insulates, and protects cables at panel entry points.
- Sizes SR 2-Series to SR 6-Series for mounting hole diameters from .375" (9,5 mm) to .500" (12,7 mm).
- See page 4-38 for corresponding **Mounting Hole Plugs** which can be used to fill blank/unused Mounting Holes and thus allow for a single panel design for multiple applications.
- See pages 4-27 & 4-28 for SR assembly tools.
- **See schematic on page 4-20.**
- For Double D Mounting Hole Punches, see page 4-30.



WILL FIT THESE CABLES				PANEL DIMENSIONS						PART NO.	DESCRIPTION	PART DIM.		Mounting									
UL Type	AWG/ Conductors	Approximate Size		A Mounting Hole Dia.		B To Prevent Rotation		Finished Fit Panel Thickness*		Black		C BODY LENGTH		Hole Plug									
		in.	mm.	in.	mm.	in.	mm.	in.	mm.			in.	mm.	PART NO.									
AWM	12/1	.125- .187	3,2- 4,8	.375	9,5	.330	8,4	.062	1,6	1060	SR 2M-1	.406	10,3	2617									
SV & SVT	18/2	.220- .245	5,6- 6,2	.500	12,7	.450	11,4	.062	1,6	1157	SR 5MN-3	.438	11,1	2491									
Same as SR 5MN-3 above except								.100	2,5	1140	SR 5M-3	.438	11,1	2491									
For custom interlock cable, not UR		.250	6,4	.560	14,2	.730	18,5	.125	3,2	1487	SR 30-1A**	.672	17,1	consult Heyco									
		.265	6,7	.560	14,2	.730	18,5	.125	3,2	1490	SR 30-1B**												
SV & SVT	18/2	.250	6,4	.500	12,7	.450	11,4																
	18/3	.255	6,5	.500- .515	12,7- 13,1																		
HPD	18/2	.270	6,9	.500	12,7	.450	11,4	.062	1,6	1150	SR 5N-4	.438	11,1	2491									
	16/2	.290	7,4	.500- .515	12,7- 13,1																		
SJT	18/2	.300	7,6	.531	13,5																		
Same as SR 5N-4 above except															.100	2,5	1147	SR 5P-4	.438	11,1	2491		
															.156	4,0	1154	SR 5L-1	.438	11,1	consult Heyco		
SV & SVT	18/2	.255	6,5	.500	12,7	.450	11,4	.100	2,5	1137	SR 5P3-4	.438	11,1	2491									
	18/3	.270	6,9																				
HPD	18/2	.290	7,4	.500	12,7																		
SJ, SJT & SJO	18/2	.300	7,6																				
SPT-3	16/2																						
															.090	2,3	1184	SR 6W-1	.438	11,1	2491		

Standard color black. Consult Heyco for white and other colors.

*Maximum Panel Thickness. Part has additional clearance. Consult Heyco for your Custom Finished Fit Panel Thickness.

**Use Elongated Mounting Hole.

Quick Specs

Material
Certifications

Nylon 6/6



Recognized under the Component Program of Underwriters' Laboratories File E15331



Certified by the Canadian Standards Association File 8919

Flammability Rating
Temperature Range

94V-2

-.04°F (-18°C) to 221°F (105°C)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[1157](#) [1140](#)