

Heyco® Pry Out Plugs

Standard Finger Design

Mounting Hole Diameter Range: .250" (6,4 mm) to 2.500" (63,5 mm)

MOUNTING HOLE DIAMETER		PART NO.		DESCRIPTION	PART DIMENSIONS			
in.	mm.	Black	White		A Head Diameter		B Overall Height	
					in.	mm.	in.	mm.

Clearance Fit for Panel Thickness up to .156" (4,0 mm)

.250	6,4	3053	3054	POP 250	.42	10,7	.33	8,3
------	-----	------	------	---------	-----	------	-----	-----

Clearance Fit for Panel Thickness up to .172" (4,4 mm)

.312	7,9	3056	3057	POP 312	.51	12,9	.41	10,4
.375	9,5	3059	3060	POP 375	.58	14,7		
.437	11,1	3062	3063	POP 437	.61	15,5		
.500	12,7	3065	3066	POP 500	.67	17,0		
.562	14,3	3068	3069	POP 562	.73	18,6		
.625	15,9	3071	3072	POP 625	.80	20,2		
.687	17,4	3074	3075	POP 687	.89	22,6		
.750	19,0	3077	3078	POP 750	.97	24,6		
.812	20,6	3080	3081	POP 812	1.03	26,2		
.875	22,2	3083	3084	POP 875	1.08	27,4		
1.000	25,4	3086	3087	POP 1000	1.22	30,9		
1.093	27,8	3089	3090	POP 1093	1.30	32,9		
1.187	30,1	3092	3093	POP 1187	1.41	35,7		
1.250	31,8	3095	3096	POP 1250	1.45	36,9		
1.375	34,9	3098	3099	POP 1375	1.58	40,1	.45	11,5

Clearance Fit for Panel Thickness up to .250" (6,4 mm)

1.500	38,1	3124	3125	POP 1500	1.72	43,6	.45	11,5
1.750	44,5	2973	2974	POP 1750	1.98	50,3	.48	12,2
2.000	50,8	2798	2799	POP 2000	2.22	56,4	.48	12,2
2.500	63,5	2975	2976	POP 2.5	2.69	68,4	.74	18,8

Standard color black. Consult Heyco for other colors.

Prong Finger Design

Mounting Hole Diameter Range: .187" (4,7 mm) to .375" (9,5 mm)

WILL FIT THESE PANELS								PART NO.		DESCRIPTION	HEAD STYLE	PART DIMENSIONS			
MOUNTING HOLE DIAMETER		THICKNESS RANGE		Black	Natural							A Head Diameter		B Overall Height	
Minimum	Maximum	Minimum	Maximum									in.	mm.	in.	mm.

Clearance Fit for Panel Thickness Ranges Shown


.187	4,7	.192	4,9	.031	0,8	.062	1,6	12170	12171	PPL 187	Glossy	.35	8,9	.18	4,6
.313	8,0	.318	8,1	.047	1,2	.156	4,0	12178	12179	PPL 313	Dome	.58	14,7	.41	10,4
.375	9,5	.380	9,7	.093	2,4	.312	7,9	12182	12183	PPL 375	Glossy	.19	12,4	.53	13,5

Standard color black and natural.


Material	Nylon 6/6
Certifications	 Recognized under the Component Program of Underwriters' Laboratories, File E51579 (POP Plugs only)  Certified by the Canadian Standards Association, File 8919 (POP Plugs only)
Flammability Rating	94V-2
Temperature Range	-40°F (-40°C) to 221°F (105°C) (POP Plugs only) 32°F (0°C) to 185°F (85°C) (PPL Plugs only)



- **POP in closures** for pipe and tubing ends.
- Retaining fingers without locking steps provide friction fit and allow removal of plug.
- Bumper protection.
- Flat, matte finish head.
- Multiple sizes for use in .250" (6,4 mm) to 2.500" (63,5 mm) diameter holes for panel thickness up to .250" (6,4 mm).
- Approximate Head Thickness: .062" (1,6 mm).



- Flexible and tapered prongs on plug will snugly lock in place with fingertip pressure, but can be removed & reused.
- Durable and non-conductive.
- Excellent dust protection for electronic equipment.
- Abrasion and vibration resistant.
- May be used as temporary or permanent hole plugs.
- Function as feet on small appliances.
- May be used to close tube ends.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[3053](#)