

## Heyco®-Tite Liquid Tight Cordgrips for Enphase Q Cables


Straight-Thru, NPT Hubs with Integral Sealing Ring

*The Ultimate in Liquid Tight Strain Relief Protection*

**ALL NEW  
PRODUCT!**

GLAND CONFIGURATION			PART NO.	DESCRIPTION	UL/CS or cSAus	PART DIMENSIONS									
Type	Size	No.				A	B	C	D	E					
	mm.		Black			Clearance Hole Dia.	Max. O.A. Length	Thread Length	Wrenching Nut Thickness	Flat Size					
						in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.
<b>Oval Gland</b>															
Q Cable	6,1 x 9,7	1	M3231GCZ	LTCG 1/2 6.1x9.7MM	UL/CS	.875	22,2	1.70	43,2	.61	15,5	.21	5,3	.98	24,9
<b>Break-Thru Skinned Over Gland</b>															
Q Cables plus Ground	6,1 x 9,7 3,3	2 1	M3234GDA-SM	SMCG 3/4 2-6.1x9.7MM 1-3.3MM	UL/CS	1.040	26,4	2.00	50,8	.62	15,7	.25	6,4	1.30	33,0

Metal Locknuts INCLUDED.




Material	Nylon 6/6 with TPE Sealing Gland
Certifications	<ul style="list-style-type: none"> <li>UL Listed under Underwriters' Laboratories File E504900</li> <li>CSA Certified by the Canadian Standards Association File 93876</li> </ul>
Flammability Rating	94V-2
Temperature Range	Static -40°F (-40°C) to 239°F (115°C) Dynamic -4°F (-20°C) to 212°F (100°C)
IP Rating	IP 68

## Heyco® Helios® UVX Clip – Blind Mount

**ALL NEW  
PRODUCT!**

PANEL THICKNESS RANGE				WIRE DIAMETER RANGE 1-2 Wires	PART NO.	DESCRIPTION	MOUNTING HOLE DIA.		OVERALL HEIGHT	
Minimum		Maximum					A	C		
in.	mm.	in.	mm.				in.	mm.	in.	mm.
1-2 Wires										
.028	0,7	.250	6,4	.23 (5,8 mm) - .32 (8,0 mm) each cable	S6520	Helios UVX Clip 100 Pack	.260	6,6	.96	24,4
					S6560	Helios UVX Clip Bulk				



Material	Nylon 6/6 with extended UV Capabilities
Flammability Rating	94V-2
Temperature Range	Dynamic -4°F (-20°C) to 185°F (85°C)

- Two new cordgrips now accommodate the Enphase Q Cable – M3231GCZ (1/2" NPT) and M3234GDA-SM (3/4" NPT).
- The 1/2" version provides liquid tight entry for one Enphase Q Cable – .24 x .38" (6,1 x 9,7 mm).
- The 3/4" version provides liquid tight entry for up to two Enphase Q Cables – .24 x .38" (6,1 x 9,7 mm) and an additional .130" (3,3 mm) dia. hole for a #8 solid grounding cable.
- The 3/4" version utilizes our skinned-over technology so any unused holes will retain a liquid tight seal.
- Rated for use with DG Cable.



- The jersey pine tree mounting style installs easily with superior holding power.
- UVX nylon protects from corrosion due to outdoor exposure.
- Installs into .260" (6,6 mm) mounting hole.
- Holds up to 2 cables between .230 - .315" (5,8 - 8,0 mm) each.
- Cables install with fingertip pressure.
- Molded from our robust UVX nylon 6/6 with extended UV capabilities for our Solar 20 Year Warranty.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Heyco:

[M3231GCZ](#) [M3234GDA-SM](#) [S6520](#) [M3234GDA-SM-P](#) [M3231GCZ-P](#) [S6560](#) [M3234GDC](#)