

"Stay Connected" with

HEYCO®

Bushings, Grommets, HEYcaps & Plugs

a PennEngineering® Company



Heyco® Nylon Liquid Tight Threaded Plugs

Liquid Tight, with Integral Sealing Ring
Hex Head with Slot

**NO O-RING
REQUIRED!**

- **Integral sealing ring** ensures a superior seal at mounting hole location, every time.
- IP 68 Rated.
- Provide a liquid-tight seal up to 70 psi.
- UL Rated for Type NEMA 3R, 4 and 4X applications.
- Threaded plugs for hydraulic and pneumatic applications.
- Seal threaded openings and protect against contamination and moisture.
- Lower cost option over brass or steel plugs.
- Non-corrosive—resist salt water, weak acids, gasoline, alcohol, oil, grease, and common solvents.
- Resist oil and heat up to 221°F (105°C).
- Approximate Head Thickness: .21" (5,3 mm). Thickness may vary.
- Hex shaped head with slot for wrench or screwdriver installation.
- Electrically non-conductive Nylon 6/6.

THREAD TYPE/SIZE	PART NO.			DESCRIPTION	PART DIMENSIONS			
	Black	Gray	V-0 Black NEW		A Wrenching Flats		B Overall Length	
					in.	mm.	in.	mm.

NPT

NPT 1/4	3544B	3544	-	LTTP NPT 1/4	.63	16,0	.66	16,8
NPT 3/8	3545B	3545	-	LTTP NPT 3/8	.83	21,1	.69	17,5
NPT 1/2	3546B	3546	V3546*	LTTP NPT 1/2	.98	24,9	.81	20,6
NPT 3/4	3547B	3547	V3547*	LTTP NPT 3/4	1.29	32,8	.86	21,8
NPT 1*	3548B	3548	V3548	LTTP NPT 1	1.74	44,2	1.05	26,7
NPT 1-1/4*	3549B	3549	V3549	LTTP NPT 1-1/4	2.06	52,3	1.08	27,4

PG - for PG Thread Specifications, see page 3-49

PG 7	3574B	3574	-	LTTP PG 7	.63	16,0	.53	13,5
PG 9	3575B	3575	-	LTTP PG 9	.83	21,0		
PG 13.5	3576B	3576	-	LTTP PG 13.5	.98	24,9	.62	15,8
PG 21	3401B	3401	-	LTTP PG 21	1.29	32,8	.68	17,3
PG 29*	3578B	3578	-	LTTP PG 29	1.74	44,2	.87	22,1
PG 36*	3579B	3579	-	LTTP PG 36	2.06	52,3	.78	19,8

Metric

M12	3582B	3582	-	LTTP M12	.63	16,0	.53	13,5
M16	3583B	3583	-	LTTP M16	.83	21,1		
M20	3584B	3584	-	LTTP M20	.98	24,9	.62	15,8
M25	3585B	3585	-	LTTP M25	1.29	32,8	.76	19,3
M32*	3586B	3586	-	LTTP M32	1.74	44,2	.87	22,1
M40*	3587B	3587	-	LTTP M40	2.06	52,3	.78	19,8



Standard colors black and gray. Consult Heyco for other colors, and sizes in V-0 material.

*Not cURus.

Available in Small Packs

PART NO.	DESCRIPTION	QTY
3546-P	LTTP NPT 1/2 Gray 100PK	100
3547-P	LTTP NPT 3/4 Gray 100PK	100
3548-P	LTTP NPT 1 Gray 100PK	100
3549-P	LTTP NPT 1-1/4 Gray 50PK	50

Standard color gray.



*Quick
Specs*

Material	Nylon 6/6
Certifications	c us Recognized under the Component Program of Underwriters' Laboratories, File E330194 to both Canadian and U.S. Requirements
Flammability Rating	94V-2
Temperature Range	-40°F (-40°C) to 221°F (105°C)
IP Rating	IP 68 (70 PSI, 5 BAR)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[3585B](#) [3585](#)