

“Stay Connected” with



Liquid Tight Conduit, Tubing & Fittings

a PennEngineering® Company




## Heyco-Flex™ III Nylon 94V-0 Corrugated Liquid Tight Tubing

Flexible, Nonmetallic Liquid Tight Electrical Tubing

- Corrugated tubing for trade sizes 3/8” through 1”.
- Flame retardant, won’t burn.
- Nontoxic and UV resistant.
- **Rated for NEMA 4 and 4X applications when used with Heyco-Flex III Liquid Tight Fittings.**
- Rated for NEMA Type 3R applications.
- Maximum flexibility, can be used in extremely tight quarters. Bend radius of Heyco-Flex III is equal to its outside diameter.
- No threading of the tubing required to install. This eliminates the possibility of cutting the tubing and creating leak paths.
- Easy, permanent assembly between the tubing and fittings: push the tubing over the fitting ferrule until the tubing clicks into place.
- Lightweight and lower installed cost.
- Quick and easy installation.
- For use with Heyco-Flex III Fittings, See page 2-2.
- Resists corrosion, oil, and water.
- For use in both wet and dry applications.
- Suitable for use in high vibration or flexing applications (automotive equipment, fiber optics, computer and peripherals, lab equipment, robotics, etc.).
- **Voltage Rating: 300V.**
- **Mounting brackets are available, see page 2-19.**
- **Order Part No. 8340**, HF-28 Cutting Tool, for cutting Heyco-Flex Tubing cleanly and evenly. See page 2-8.
- For additional nylon conduit sizes, see page 2-3.

TRADE SIZE	PART NO. Black	DESCRIPTION	PART DIMENSIONS				STANDARD COIL LENGTH*
			A Outside Diameter		B Inside Diameter		
			in.	mm.	in.	mm.	ft/coil
3/8	<b>8478</b>	HF3 3/8 FR	.71	18,0	.51	13,1	100
1/2	<b>8479</b>	HF3 1/2 FR	.85	21,6	.65	16,5	
3/4	<b>8480</b>	HF3 3/4 FR	1.12	28,3	.87	22,0	
1	<b>8481</b>	HF3 1 FR	1.35	34,3	1.10	28,0	

Standard color black. Consult Heyco for gray and other colors.  
\*Consult Heyco for “cut to length” and slit tubing availability.



Material	Halogen Free Nylon 6
Certifications	<b>cRUUS</b> Certified to both Canadian and U.S. Requirements under File E121095
Flammability Rating	94V-0
Temperature Range	-4°F (-18°C) to 221°F (105°C)



## Heyco® Female Threaded Couplings

For Heyco HF3C and other NPT Hub Components

- Both ends feature female NPT threads for joining various male NPT hub parts.
- Facilitate the connection between Heyco-Flex III Fittings (HF3C – page 2-2), Conduit (HF3 – above), and the various Heyco Liquid Tight Cordgrips (Section 3) typically used in solar installations.

TRADE SIZE	PART NO. Gray	DESCRIPTION
1/2	<b>8665</b>	FTC 1/2
3/4	<b>8666</b>	FTC 3/4
1	<b>8667</b>	FTC 1
1-1/4	<b>8668</b>	FTC 1-1/4
1-1/2	<b>8669</b>	FTC 1-1/2
2	<b>8670</b>	FTC 2

Material	Schedule 80 PVC
----------	-----------------

Quick Specs

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[8481](#) [8480](#) [8479](#) [8478](#) [8665](#) [8666](#) [8667](#) [8668](#) [8669](#) [8670](#)