




## Heyco® Extra Dome Plugs

Multiple Locking Steps for Panel Thickness up to .250" (6,4 mm)

MOUNTING HOLE DIAMETER		PART NO.		DESCRIPTION	PART DIMENSIONS					
		Black	White		A Head Diameter		B Overall Height		C Inside Height	
in.	mm.				in.	mm.	in.	mm.	in.	mm.
3.0	76,2	2442	2443	EDP 3.0	3.22	81,8	1.37	34,8	1.26	32,0
5.0	127,0	2444	2445	EDP 5.0	5.22	132,6	1.41	35,8	1.31	33,3

Standard colors black. Consult Heyco for other colors.



- **Extra dome height** for additional clearance under the top.
- Consult Heyco for additional sizes.
- Lock firmly into panels up to .250" (6,4 mm) thick.
- Locking fingers in fractional increments up to the maximum panel thickness.
- Not UL Recognized.




## Heyco® Snap-In Metric Dome Plugs

Multiple Locking Steps for Panel Thickness up to 4,1 mm (.162")

Mounting Hole Diameter Range: 13,0 mm (.512") to 34,2 mm (1.347")

MOUNTING HOLE DIAMETER		PART NO.		DESCRIPTION	PART DIMENSIONS			
		Black	White		A Head Diameter		B Overall Height	
mm.	in.				mm.	in.	mm.	in.
13,0	.512	2203	2204	MDP 13	14,2	.56	10,3	.406
16,0	.630	2128	2130	MDP 16	18,5	.73		
20,0	.787	2131	2132	MDP 20	22,6	.89		
22,0	.866	2205	2206	MDP 22	25,9	1.02	11,5	.453
25,0	.984	2133	2134	MDP 25	29,8	1.17		
28,0	1.102	2215	2216	MDP 28	31,2	1.23		
32,0	1.260	2135	2136	MDP 32	35,3	1.38		
34,2	1.347	2218	2219	MDP 34	38,1	1.50		

Standard color black. Consult Heyco for other colors.



- Multiple sizes for use in **13,0 mm (.512") to 34,2 mm (1.347") diameter holes**. For other metric sizes, consult Heyco.
- Close unneeded panel holes.
- Quick and easy installation.
- Convex, matte finish head tapers to a thin edge.
- Lock firmly into panel up to 4,1 mm (.162") thick.
- Approximate Head Thickness: 1,6 mm (.062").
- For **Threaded Metric Plugs**, see page 6-44.
- For our complete range of Dome Plugs, see pages 6-25 and 6-26.

Material  
Certifications



Nylon 6/6  
Recognized under the Component Program of Underwriters' Laboratories,  
File E51579 (MDP's only)



Certified by Canadian Standards Association, File 8919 (MDP's only)

Flammability Rating  
Temperature Range

94V-2  
-40°F (-40°C) to 221°F (105°C)

*Quick  
Specs*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[2128](#) [2133](#) [2135](#) [2134](#) [2136](#) [2130](#) [2132](#) [2216](#) [2219](#) [2205](#) [2215](#) [2218](#) [2203](#) [2206](#) [2204](#) [2133-P](#) [2128-P](#)  
[2205-P](#) [2135-P](#) [2131GU](#) [2136-P](#) [2203-P](#) [2204-P](#) [2206-P](#) [2218-P](#) [2219-P](#)