

**"Stay Connected" with**



**Liquid Tight Cordgrips**

a PennEngineering® Company

## Heyco® -Tite Liquid Tight Cordgrips

**Multi-Hole** with Integral Sealing Ring

Sequenced by Conductor Size

*The Ultimate in Liquid Tight Strain Relief Protection*

**NO O-RING  
REQUIRED!**



CONDUCTORS		NPT HUB*		PG HUB**		METRIC HUB**	
Hole Size mm.	No.	UL or cULus	specifications on page 3-1 Black Part No. Desc.	specifications on page 3-3 Black Part No. Desc.	specifications on page 3-3 Black Part No. Desc.	specifications on page 3-4 Black Part No. Desc.	specifications on page 3-4 Black Part No. Desc.
<b>Round, Open Holes – consult Heyco for Snap-in-2 Hub versions</b>							
4,2	2		M3231GAB LTCG 1/2	M3216GAB LTCG 13	M4340GAB LTCG M20		
4,5	9	cULus	M8437GBF† LTCG 1	M3225GBF LTCG 29	M4348GBF LTCG M32		
	13	cULus	M4524GBG† LTCG 1-1/4	M3204GBG LTCG 36	M4352GBG LTCG M40		
4,6	3		M3234GBD LTCG 3/4	M3222GBD LTCG 21	M4344GBD LTCG M25		
	4		M3234GBE LTCG 3/4	M3222GBE LTCG 21	M4344GBE LTCG M25		
5,0	2		M3231GAC LTCG 1/2	M3216GAC LTCG 13	M4340GAC LTCG M20		
	4		M3234GAD LTCG 3/4	M3222GAD LTCG 21	M4344GAD LTCG M25		
5,2	2	UL	M3231GAE† LTCG 1/2	M3216GAE LTCG 13	M4340GAE† LTCG M20		
	3	UL	M3234GAF† LTCG 3/4	M3222GAF LTCG 21	M4344GAF LTCG M25		
	4	UL	M3234GAG† LTCG 3/4	M3222GAG LTCG 21	M4344GAG LTCG M25		
5,6	3	UL	M3200GAH† LTCG LL 1/2	M3219GAH LTCG 16	M3198GAH LTCG LL M20		
6,0	2		M3200GAJ LTCG LL 1/2	M3219GAJ LTCG 16	M3198GAJ LTCG LL M20		
	4		M3234GBC LTCG 3/4	M3222GBC LTCG 21	M4344GBC LTCG M25		
6,5	6		M8437GAL LTCG 1	M3225GAL LTCG 29	M4348GAL LTCG M32		
			M4524GAL LTCG 1-1/4	M3204GAL LTCG 36	M4352GAL LTCG M40		
7,0	3		M3234GAM LTCG 3/4	M3222GAM LTCG 21	M4344GAM LTCG M25		
7,4	2		M3234GAN LTCG 3/4	M3222GAN LTCG 21	M4344GAN LTCG M25		
8,0	2		M3234GAQ LTCG 3/4	M3222GAQ LTCG 21	M4344GAQ LTCG M25		
	6		M4524GAR LTCG 1-1/4	M3204GAR LTCG 36	M4352GAR LTCG M40		
9,0	4		M8437GAS LTCG 1	M3225GAS LTCG 29	M4348GAS LTCG M32		
	5		M4524GAT LTCG 1-1/4	M3204GAT LTCG 36	M4352GAT LTCG M40		
	7		M4524GAW LTCG 1-1/4	M3204GAW LTCG 36	M4352GAW LTCG M40		
9,5	4		M8437GAX LTCG 1	M3225GAX LTCG 29	M4348GAX LTCG M32		

Standard color black.

**\*Locknuts not included.** For Locknut specifications or to order Locknuts separately, see pages 3-47 & 3-48.

**\*\*Unassembled Nylon Locknuts INCLUDED.**

**†Assembled Metal Locknut INCLUDED**

**††M4340GAE is UL approved under File E51579**



Material	Nylon 6/6 with TPE Sealing Gland
Certifications	UL Listed under Underwriters' Laboratories File E51579 cULus Recognized under the Component Program of Underwriters' Laboratories File E51579 to both Canadian and U.S. requirements
Flammability Rating	94V-2 Standard
Temperature Range	Static -40°F (-40°C) to 239°F (115°C) Dynamic -4°F (-20°C) to 212°F (100°C)
IP Rating	IP 68

*Quick  
Specs*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Heyco:

[M3200GAH](#) [M3200GAJ](#) [M3222GAQ](#) [M3231GAB](#) [M3231GAC](#) [M3231GAE](#) [M3234GAD](#) [M3234GAF](#) [M3234GAG](#)  
[M3234GAM](#) [M3234GAN](#) [M3234GAQ](#) [M3234GBC](#) [M4524GAL](#) [M4524GAR](#) [M4524GAT](#) [M4524GAW](#) [M8437GAL](#)  
[M8437GAS](#) [M8437GAX](#) [M8437GBF](#) [M4524GBG](#) [M3204GAW](#) [M3216GAC](#) [M3222GAM](#) [M3222GAG](#) [M3222GBD](#)  
[M3225GAS](#) [M4340GAE](#) [M3219GAH](#) [M3216GAE](#) [M3216GAB](#) [M3234GBD](#) [M3198GAJ](#) [M3222GAF](#) [M3219GAJ](#)  
[M3198GAH](#) [M3225GAX](#) [M3222GBC](#) [M3204GAL](#) [M3222GAD](#) [M3204GAR](#) [M3222GAN](#) [M3204GAT](#) [M3225GAL](#)  
[M3222GBE](#) [M3225GBF](#) [M3234GBE](#) [M3204GBG](#) [M3222GA](#) [M3223GA](#) [M3234GAA](#) [M3214GAY](#) [M3232GAB](#)  
[M3448GB](#) [M3223GAM](#) [M3223GBD](#) [M3232GAE](#) [M8438GAL](#) [M3226GAX](#) [M4747GBR](#) [M3232GAC](#) [M4525GAT](#)  
[M3235GBD](#) [M3214GAK](#) [M3203GAT](#) [M3211GAZ](#) [M3203GAL](#) [M3226GBL](#) [M3229GAZ](#) [M3201GAH](#) [M3235GAM](#)  
[M8438GAX](#) [M3223GBC](#) [M3235GBC](#) [M3223GAG](#) [M8438GAS](#) [M3201GBB](#) [M3235GBE](#) [M3223GAF](#) [M3235GAQ](#)  
[M3217GAE](#) [M3223GAQ](#) [M3203GAR](#) [M3220GAJ](#) [M4525GAW](#) [M3235GAG](#) [M3211GAP](#) [M3226GAS](#) [M3225GBL](#)  
[M3201GAJ](#) [M3223GBE](#) [M3220GBB](#) [M3203GAW](#) [M4525GAR](#) [M3223GAN](#) [M3235GAD](#) [M3226GAL](#) [M3220GAH](#)  
[M3223GAD](#)