

"Stay Connected" with



Liquid Tight Cordgrips

a PennEngineering® Company

Heyco® -Tite Liquid Tight Cordgrips









Multi-Hole with Integral Sealing Ring

Sequenced by Conductor Size

The Ultimate in Liquid Tight Strain Relief Protection

**NO O-RING
REQUIRED!**



CONDUCTORS		 or 	NPT HUB*		PG HUB**		METRIC HUB**	
Hole Size mm.	No.		<i>specifications on page 3-1</i>		<i>specifications on page 3-3</i>		<i>specifications on page 3-4</i>	
			Black Part No.	Desc.	Black Part No.	Desc.	Black Part No.	Desc.
Round, Open Holes – consult Heyco for Snap-in-2 Hub versions								
4,2	2		M3231GAB	LTCG 1/2	M3216GAB	LTCG 13	M4340GAB	LTCG M20
4,5	9		M8437GBF†	LTCG 1	M3225GBF	LTCG 29	M4348GBF	LTCG M32
	13		M4524GBG†	LTCG 1-1/4	M3204GBG	LTCG 36	M4352GBG	LTCG M40
4,6	3		M3234GBD	LTCG 3/4	M3222GBD	LTCG 21	M4344GBD	LTCG M25
	4		M3234GBE	LTCG 3/4	M3222GBE	LTCG 21	M4344GBE	LTCG M25
5,0	2		M3231GAC	LTCG 1/2	M3216GAC	LTCG 13	M4340GAC	LTCG M20
	4		M3234GAD	LTCG 3/4	M3222GAD	LTCG 21	M4344GAD	LTCG M25
5,2	2		M3231GAE†	LTCG 1/2	M3216GAE	LTCG 13	M4340GAE††	LTCG M20
	3		M3234GAF†	LTCG 3/4	M3222GAF	LTCG 21	M4344GAF	LTCG M25
	4		M3234GAG†	LTCG 3/4	M3222GAG	LTCG 21	M4344GAG	LTCG M25
5,6	3		M3200GAH†	LTCG LL 1/2	M3219GAH	LTCG 16	M3198GAH	LTCG LL M20
6,0	2		M3200GAJ	LTCG LL 1/2	M3219GAJ	LTCG 16	M3198GAJ	LTCG LL M20
	4		M3234GBC	LTCG 3/4	M3222GBC	LTCG 21	M4344GBC	LTCG M25
6,5	6		M8437GAL	LTCG 1	M3225GAL	LTCG 29	M4348GAL	LTCG M32
			M4524GAL	LTCG 1-1/4	M3204GAL	LTCG 36	M4352GAL	LTCG M40
7,0	3		M3234GAM	LTCG 3/4	M3222GAM	LTCG 21	M4344GAM	LTCG M25
7,4	2		M3234GAN	LTCG 3/4	M3222GAN	LTCG 21	M4344GAN	LTCG M25
8,0	2		M3234GAQ	LTCG 3/4	M3222GAQ	LTCG 21	M4344GAQ	LTCG M25
	6		M4524GAR	LTCG 1-1/4	M3204GAR	LTCG 36	M4352GAR	LTCG M40
9,0	4		M8437GAS	LTCG 1	M3225GAS	LTCG 29	M4348GAS	LTCG M32
	5		M4524GAT	LTCG 1-1/4	M3204GAT	LTCG 36	M4352GAT	LTCG M40
	7		M4524GAW	LTCG 1-1/4	M3204GAW	LTCG 36	M4352GAW	LTCG M40
9,5	4		M8437GAX	LTCG 1	M3225GAX	LTCG 29	M4348GAX	LTCG M32

Standard color black.

***Locknuts not included.** For Locknut specifications or to order Locknuts separately, see pages 3-47 & 3-48.

****Unassembled Nylon Locknuts INCLUDED.**

†Assembled Metal Locknut INCLUDED

††M4340GAE is UL approved under File E51579



Material	Nylon 6/6 with TPE Sealing Gland
Certifications	UL Listed under Underwriters' Laboratories File E51579
Flammability Rating	94V-2 Standard
Temperature Range	Static -40°F (-40°C) to 239°F (115°C) Dynamic -4°F (-20°C) to 212°F (100°C)
IP Rating	IP 68

*Quick
Specs*

- Heyco® **Multi-hole glands** provide the widest range of conductor through-hole size and number configurations, many of which are agency approved. See the tabular charts for specific approvals for specific parts. These approvals are not "global" or implied approvals; they are both real and part specific.
- Integral Sealing Ring ensures a superior seal at the clearance or threaded mounting hole location, every time.
- IP 68 rated.
- Cordgrips are made of nylon construction with TPE sealing glands that resist salt water, weak acids, gasoline, alcohol, oil, grease, and common solvents.
- For body part dimensions see page 3-1, 3-3, and 3-4.
- Multi-hole glands are only to be used with Heyco Liquid Tight Cordgrips and are not sold separately.
- Consult Heyco for Cordgrips molded in other colors.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[M3200GAH](#) [M3200GAJ](#) [M3222GAQ](#) [M3231GAC](#) [M3231GAE](#) [M3234GAD](#) [M3234GAF](#) [M3234GAG](#) [M3234GAM](#)
[M3234GAN](#) [M3234GAQ](#) [M3234GBC](#) [M4524GAL](#) [M4524GAR](#) [M4524GAT](#) [M4524GAW](#) [M8437GAL](#) [M8437GAS](#)
[M8437GAX](#) [M8437GBF](#) [M4524GBG](#) [M3204GAW](#) [M3219GY](#) [M3222GAM](#) [M3222GAG](#) [M3222GBD](#) [M3225GAS](#)
[M3219GZ](#) [M3219GW](#) [M3219GQ](#) [M3219GR](#) [M3219GBB](#) [M3219GS](#) [M3219GX](#) [M3234GBD](#) [M4344GBE](#) [M3198GAJ](#)
[M3222GAF](#) [M3219GAJ](#) [M3198GAH](#) [M3225GAX](#) [M3222GBC](#) [M3204GAL](#) [M3222GAD](#) [M4344GBD](#) [M3204GAR](#)
[M3222GAN](#) [M3204GAT](#) [M3225GAL](#) [M3222GBE](#) [M3225GBF](#) [M3234GBE](#) [M3204GBG](#) [M4348GBF](#) [M4352GBG](#)
[M3219GBH](#) [M3222GA](#) [M3223GA](#) [M3234GAA](#) [M3214GAY](#) [M3232GAB](#) [M3448GB](#) [M3223GAM](#) [M3223GBD](#)
[M3232GAE](#) [M8438GAL](#) [M3226GAX](#) [M4747GBR](#) [M3232GAC](#) [M4525GAT](#) [M3235GBD](#) [M3214GAK](#) [M3203GAT](#)
[M3211GAZ](#) [M3203GAL](#) [M3226GBL](#) [M3229GAZ](#) [M3201GAH](#) [M3235GAM](#) [M8438GAX](#) [M3223GBC](#) [M3235GBC](#)
[M3223GAG](#) [M8438GAS](#) [M3201GBB](#) [M3235GBE](#) [M3223GAF](#) [M3235GAQ](#) [M3217GAE](#) [M3223GAQ](#) [M3203GAR](#)
[M3220GAJ](#) [M4525GAW](#) [M3235GAG](#) [M3211GAP](#) [M3226GAS](#) [M3225GBL](#) [M3201GAJ](#) [M3223GBE](#) [M3220GBB](#)