


"Stay Connected" with



HEYware Products

a PennEngineering® Company



Heyco® Nytye® Push Mount Nylon Cable Ties


PART SPECIFICATIONS				PART NO.		DESCRIPTION	PART DIMENSIONS										STYLE
Tensile Strength		Max. Bundle Diameter		Natural	UV Black		A Length		B Width		C Spacer Height		Max. Panel Thickness		Mounting Hole Dia.		
Lbs.	N	in.	mm.				in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	
Tension Wings																	
40	178	1.42	36,0	-	3907†	PWMS-155-HSB	6.23	158	.14	3,5	-	-	.09	2,3	.187	4,7	1
50	222	1.57	40,0	13254	13254B	PMT-50-070	7.09	180	.19	4,8	-	-	.09	2,4	.187	4,7	2
		1.75	44,5	3904	3905	PMT 150	8.00	203	.19	4,8	-	-	.13	3,2	.250	6,4	1
Tension Wings, Standoff																	
18	80	.75	19,1	13262	13262B	PMST-18-050-156	5.04	128	.10	2,5	.24	6,1	.08	2,0	.156	4,0	3
40	178	1.38	35,0	13267	13267B	PMST-40-066-197	6.69	170	.14	3,6	.51	13,0	.08	2,0	.197	5,0	
		1.25	31,8	13268	13268B	PMST-40-068-187	6.81	173	.14	3,6	.78	19,8	.08	2,0	.187	4,7	
Cupped Base, Standoff, Releasable																	
30	133	1.25	31,8	13273	13273B	PMRS-30-066	6.63	168	.14	3,6	.53	13,5	.023 - .098	0,6 - 2,5	.236 - .255	6,0 - 6,5	4
Blind Mount - 2PC*																	
50	222	2.13	54,1	13285	13285B	PMBMT-50-079-5	7.87	200	.19	4,8	-	-	.197	5,0	.177 - .197	4,5 - 5,0	5
				13286	13286B	PMBMT-50-079-7	7.87	200	.19	4,8	-	-	.276	7,0	.256 - .276	6,5 - 7,0	
Blind Mount - 1PC**																	
50	222	1.97	50,0	13288	13288B	PMBMT-50-081-71	8.11	206	.19	4,8	-	-	.281	7,1	.250 - .270	6,4	6

Standard color natural and UV Black. Consult Heyco for heat-stabilized material and colors.


† cURus

*Discrete blind mount fastener is pre-assembled to the Nytye. **Constructed so that the discrete blind mount fastener is molded to the Nytye.


Style 1




Style 2




Style 3




Style 4



Style 5



Style 6



Quick
Specs

Material: Nylon 6/6
Flammability Rating: 94V-2
Temperature Range: -40°F (-40°C) to 185°F (85°C)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[3904](#) [13268H](#) [13285B](#) [13288B](#) [13286B](#)